



CONVERSION CHART		CONVERSION CHART	
INCH	MM	INCH	MM
.003	0,08	.500	12,70
.004	0,10	.512	13,00
.008	0,20	.527	13,38
.012	0,30	.591	15,00
.020	0,50	.625	15,87
.028	0,70	.685	17,40
.031	0,80	.709	18,00
.062	1,58	.740	18,80
.126	3,20	.882	22,41
.157	4,00	.937	23,81
.158	4,10	.984	25,00
.251	6,38	1.195	30,35
.281	7,14	1.252	31,80
.374	9,50		
.445	11,30		



# 6 SPECIFICATIONS:

MATERIALS:  
MATERIAL: ALUMINIUM, ANODIZED  
FINISH: SEE TABLE.  
SET SCREW: #6-32 UNC-2A  
STAINLESS STEEL.

# 6 NOTES:

1. INTERPRET DRAWING PER ASME Y14.5M-1994.

MODEL NO.	A	B	C	D	ANODIZE	INDICATOR LINE	TE PN
KLN500A1/8	.500	.374	.445	.126	CLEAR	BLACK	9-1437621-7
KLN500A1/4	.500	.374	.445	.251	CLEAR	BLACK	9-1437621-6
KLN500B1/8	.500	.374	.445	.126	BLACK	WHITE	9-1437621-9
KLN500B1/4	.500	.374	.445	.251	BLACK	WHITE	9-1437621-8
KLN500S1/8	.500	.374	.445	.126	SMOKE	WHITE	5-1437623-1
KLN500S1/4	.500	.374	.445	.251	SMOKE	WHITE	1437622-1
KLN700A1/4	.740	.591	.685	.251	CLEAR	BLACK	1437622-2
KLN700B1/4	.740	.591	.685	.251	BLACK	WHITE	1437622-3
KLN700B1/8	.740	.591	.685	.126	BLACK	WHITE	1437622-4
KLN700S1/4	.740	.591	.685	.251	SMOKE	WHITE	1437622-5
KLN900A1/4	.937	.709	.882	.251	CLEAR	BLACK	1437622-6
KLN900B1/4	.937	.709	.882	.251	BLACK	WHITE	1437622-7
KLN900S1/4	.937	.709	.882	.251	SMOKE	WHITE	1437622-8
KLN1250A1/4	1.252	.984	1.195	.251	CLEAR	BLACK	9-1437621-4
KLN1250B1/4	1.252	.984	1.195	.251	BLACK	WHITE	9-1437621-5
KLN1250S1/4	1.252	.984	1.195	.251	SMOKE	WHITE	4-1437623-9

OBSOLETE

4  
4  
4  
OBSOLETE

OUTLINE DRAWING					
SPECIFICATIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE					
<p>THIRD ANGLE PROJECTION</p> <p>TOLERANCES (EXCEPT AS NOTED) ANGULAR = ±3° (NON-CUMULATIVE) DECIMAL .XX = ± DECIMAL .XXX = ±.012 DECIMAL .XXXX = ±</p>	<p>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES DO NOT SCALE PRINT</p>	<p>ORIGINAL DATE OF DRAWING: 9/30/91</p>	<p>THIS IS A C.A.D. GENERATED DRAWING. DO NOT MAKE MANUAL REVISIONS TO MASTER.</p>		
	<p>FILE NAME: 802510UT</p>	<p>DIRECTORY: H0WR/KNOBS</p>		<p>DRAWN: B.R.</p>	<p>DATE: 9/30/91</p>
	<p>MATERIAL: SEE SPECIFICATIONS</p>			<p>CHECKED: CMM</p>	<p>DATE: 10/10/91</p>
	<p>FINISH: SEE SPECIFICATIONS</p>			<p>APPROVED: D.S.</p>	<p>DATE: 10/10/91</p>
		<p>CODE IDENT. NO. 91506</p>	<p>DWG. SIZE C</p>	<p>TITLE: OUTLINE DRAWING KNOB (KLN SERIES)</p>	
		<p>NEXT ASSY:</p>	<p>SCALE:</p>	<p>DWG. NO. C-1437622-1</p>	
				<p>PRODUCT CODE: M11</p>	
				<p>REVISION RECORD</p>	
				<p>DATE DWN APVD</p>	

B	REVISED PER ECO-14-000326	13JAN2014	KH	RH
P	LTR	REVISION RECORD	DATE	DWN APVD

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[KLN500B1/8](#)