









PER DETAIL Y	PER DETAIL K	K	GRAY	1438894-2	CURRY	1-1438893-0	6-1438922-0
PER DETAIL Y	PER DETAIL H	H	GRAY	1438894-2	HEATHER VIOLET	1438893-8	5-1438922-8
PER DETAIL Y	PER DETAIL D	D	GRAY	1438894-2	CLARET VIOLET	1438893-4	5-1438922-4
PER DETAIL Y	PER DETAIL C	C	GRAY	1438894-2	SIGNAL BLUE	1438893-3	5-1438922-3
PER DETAIL Y	PER DETAIL B	B	GRAY	1438894-2	SIGNAL WHITE	1438893-2	5-1438922-2
-	-	-	-	-	-	-	5-1438922-1
PER DETAIL X	PER DETAIL K	K	RED	1438888-1	CURRY	1-1438893-0	1-1438922-0
PER DETAIL X	PER DETAIL H	H	RED	1438888-1	HEATHER VIOLET	1438893-8	1438922-8
PER DETAIL X	PER DETAIL D	D	RED	1438888-1	CLARET VIOLET	1438893-4	1438922-4
PER DETAIL X	PER DETAIL C	C	RED	1438888-1	SIGNAL BLUE	1438893-3	1438922-3
PER DETAIL X	PER DETAIL B	B	RED	1438888-1	SIGNAL WHITE	1438893-2	1438922-2
-	-	-	-	-	-	-	1438922-1
ASSEMBLY	KEYING	CODING	LOCK COLOR	LOCK PART NUMBER	HOUSING COLOR	PLUG HOUSING PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN D. J. HARDY 04JAN2005	TE Connectivity	
DIMENSIONS:		CHK J. W. HALL 19JAN2005	NAME PLUG KIT, UNASSEMBLED, 1 POSITION, RG-62U/M, 180 DEGREE, FAKRA, SMB	
mm		APVD J. W. HALL 19JAN2005	PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		
9 PLC ±		SIZE		
1 PLC ±		CAGE CODE		
2 PLC ±0.25		DRAWING NO		
3 PLC ±		RESTRICTED TO		
4 PLC ±		A100779C=1438922		
ANGLES		WEIGHT		
FINISH		CUSTOMER DRAWING		
MATERIAL		SCALE 4:1 SHEET 1 OF 2 REV D1		


LOC		DIST		REVISIONS					
IN		00		REV	LYR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-




DETAIL B
SCALE 5:1




DETAIL C
SCALE 5:1



DETAIL D
SCALE 5:1



DETAIL H
SCALE 5:1



DETAIL K
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN D. J. HARDY 04JAN2005		 TE Connectivity			
DIMENSIONS:			CHK J. W. HALL 19JAN2005					
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APRD J. W. HALL 19JAN2005		NAME		
		0 PLC ±:		PRODUCT SPEC		PLUG KIT, UNASSEMBLED, 1 POSITION, RG-62U/M, 180 DEGREE, FAKRA, SMB		
		1 PLC ±:		APPLICATION SPEC				
		2 PLC ±0.25		SIZE CAGE CODE DRAWING NO				
		3 PLC ±:		RESTRICTED TO				
MATERIAL		4 PLC ±:		114-13157		A100779C=1438922		
FINISH		5 PLUG ±:		WEIGHT		SCALE 4:1 SHEET 2 OF 2 REV D		
		6 PLUG ±:		CUSTOMER DRAWING				
		ANGLES						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1438922-2](#)