


REVISIONS				
ZONE	LTR	ECN	DESCRIPTION	DATE
	J	25602	REV. & REDRAWN. ORIGINAL RELEASE 8-17-64 BY B.T. & J.C.B. CB 2-5-81	2-6-81
	K	38873	REVISION UPDATE	4-22-99



Tyco Dwg 1466115
Micro P/N 03202170022

NOTES: UNLESS OTHERWISE SPECIFIED

- THIS CONNECTOR MATES WITH ALL JACKS AND RECEPTACLES IN SERIES S-50 AS LISTED IN MALCO CATALOG.
- FOR ASSEMBLY INSTRUCTIONS SEE RF-ASMB-88. USE MALCO SPECIAL TOOL #010-0003-0000.
- SILVER PLATE .0002 MIN. PER QQ-S-365, TYPE II, GRADE A.
- GOLD PLATE PER MIL-G-45204 TYPE II, GRADE C, CLASS I.
- CABLE ACCEPTANCE DIMENSIONS:
JACKET: .087 DIA. MAX.
SHIELD: .061 DIA. MAX.
DIELECTRIC: .050 DIA. MAX.
INNER CONDUCTOR: .012 DIA. NOM.

1		003-0270-0002	B.R. CAP	SILICONE RUBBER (RED) PER ZZ-R-765	5
1	3	003-0163-0001	RING, JERK	BRASS PER QQ-B-626	4
1		003-0027-0001	INSULATOR	TEFLON PER L-P-403	3
1	4	003-0359-0002	PIN	BRASS PER QQ-B-626	2
		003-1081-0000	RING, SNAP	BERYLLIUM COPPER PER QQ-C-530	
	3	003-0804-0001	NUT	BRASS PER QQ-B-626	
	3	003-1083-0001	HOUSING	BRASS PER QQ-B-626	
1		003-1084-0001	HOUSING, SUBASSY.		1
QTY.	FINISH	PART NUMBER	DESCRIPTION	MATERIAL & SPECIFICATION	ITEM NO.

PARTS LIST

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± .XXX ± .010 ±		CONTRACT NO.		MALCO A MICRODOT COMPANY, INC. 306 PASADENA AVE., SO. PASADENA, CALIF. 91030	PROD. CODE 931 CODE CDM
		APPROVALS	DATE		
		DRAWN <i>Gold Proum</i>	2-6-81		
		CHECKED <i>Effan</i>	2/6/81		
MATERIAL		PR. ENG. <i>Noted</i>		2-6-81	
FINISH		APPROVED			
NOTED		NOTED			
NEXT ASSY		USED ON			
APPLICATION		DO NOT SCALE DRAWING			

SIZE	CODE IDENT NO.	DRAWING NO.
B	98278	032-0217-0022
SCALE	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1466115-1](#)