



- 1 0.00076[.000030] MIN GOLD IN CONTACT AREA, 0.00381[.000150] MIN TIN-LEAD ON SOLDER TAILS ALL OVER 0.00127[.000050] MIN NICKEL
- 2 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 3 PARTS TO BE PACKAGED IN TUBES.
- 4 PARTS TO BE PACKAGED IN TAPE AND REEL.
- 5 KAPTON VACUUM PICK-UP BUTTON FOR -2 & -4 ONLY (SHOWN IN PHANTOM TO SHOW CONNECTOR DETAIL).
- 6 0.00076[.000030] MIN GOLD IN CONTACT AREA, 0.00381[.000150] MIN TIN ON SOLDER TAILS ALL OVER 0.00127[.000050] MIN NICKEL

6	4	AS SHOWN	1,13,38, 50	ALL OTHER PINS	25,26	146839-4
6	3					146839-3
1	4					146839-2
1	3					146839-1
CONTACT FINISH	PACKAGING	DESCRIPTION	.197	.167	.138	ASSEMBLY PART NUMBER
			"L" PIN LGTH & CAVITY LOCATION			

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: J.ROOT	27JUN96	Tyco Electronics Corporation	
DIMENSIONS: min [INCHES]		CHK: V.RUMINSKI	07MAR07	Harrisburg, PA 17105-3608	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: -	NAME: -	PIN HEADER ASSEMBLY, VERTICAL, 50 POSN, SURFACE MOUNT.	
0 PLC ± -	1 PLC ± -	PRODUCT SPEC: -	APPLICATION SPEC: -	SIZE: A1	CAGE CODE: 00779
2 PLC ± 0.13[.005]	3 PLC ± -	WEIGHT: -	SCALE: 4:1	DRAWING NO: 146839	REV: 01
4 PLC ± -	ANGLES ± 2°	CUSTOMER DRAWING	SHEET 1 OF 1	RESTRICTED TO	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146839-3](#)