



- 1
- BERYLLIUM COPPER PER ASTM-B-197 OR ASTM-B-643.
- 2
- BRASS PER ASTM-B-16.
- 3
- PTFE PER ASTM-D-1710.
- 4
- GOLD PLATE PER ASTM-B-488 (MIL-G-45204), TYPE 2, GRADE C, .000050 [0.00127] MIN THK OVER NICKEL PLATE PER QQ-N-290, .000050 [0.00127] MIN THK.
- 5
- THIS AREA IS SOLDER DIPPED. (-4 ONLY)

.020±.002 [0.51±0.05]	.040±.003 [1.02±0.08]	NO	1.205 [30.61]	1484201-5
.026 [0.66] MAX	.047 [1.19] MAX	YES	1.277 [32.44]	1484201-4
.020±.002 [0.51±0.05]	.040±.003 [1.02±0.08]	NO	1.277 [32.44]	1484201-3
.020±.002 [0.51±0.05]	.040±.003 [1.02±0.08]	NO	1.249 [31.72]	1484201-2
.020±.002 [0.51±0.05]	.040±.003 [1.02±0.08]	NO	1.158 [29.41]	1484201-1
DIM B	DIM A	SOLDER DIPPED	L±.020 [±0.51]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 1-10-02	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES [mm]		CHK S.GLATFELTER 1-10-02		
		APVD S.GLATFELTER 1-10-02		NAME PIN CONTACT ASSY,COAX,SIZE 5 POSTED,ARINC 600
		PRODUCT SPEC		
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		SIZE A2
		WEIGHT —		CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C=1484201
		SCALE 8:1		SHEET 1 of 1
		REV C		RESTRICTED TO —

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1484201-1](#)