




REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APPD
C		REV PER ECO 18-010821	7-9-18	CT	PR

- FOR USE WITH THE FOLLOWING RG-11 TRIAX CABLE:
BIW 10382-C-G18
BIW 12363-C-G20
BIW 12240-C-G20
ROCKBESTOS RSS-6-109/LE
BRAND-REX TS75285
- USE CRIMPING TOOL 90415-3 WITH DIE SET 58264-2.
- ONLY 5 ITEMS ARE REQUIRED TO COMPLETE TERMINATION, SEE APPLICATION SPECIFICATION FOR DETAILS.
- * AND CUSTOMER PART NUMBER (SEE TABLE) STEEL STAMPED ON THIS SURFACE, ORIENTATION IS AMP'S OPTION.

RECOMMENDED STRIP LENGTH
SCALE 4:1

OBSOLETE	--	5-221773-3	1484833-1	1484830-1	221773-4	221773-2	1484829-2	1484829-1	5-1484794-1
	405A30-NJK	221777-3	1484833-2	1484830-2	221773-4	221773-2	1484829-2	1484829-1	1484794-2
	405A30-NJ	221777-3	1484833-1	1484830-1	221773-4	221773-2	1484829-2	1484829-1	1484794-1
CUSTOMER MARKING		7 FERRULE, INTERMEDIATE QTY=1	6 SHELL ASSY, OUTER QTY=1	5 SHELL ASSY, INNER QTY=1	4 FERRULE, INNER QTY=1	3 FERRULE, INNER QTY=1	2 CONTACT, ASSY QTY=1	1 CONTACT, ASSY QTY=1	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN C.C.THOMAS	08APR2002
DIMENSIONS: INCHES		CHK R.GROSS	4-8-02
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPD R.GROSS	NAME
0 PLC ± -		PRODUCT SPEC	
1 PLC ± -		108-12094	
2 PLC ± -		APPLICATION SPEC	
3 PLC ± .018 [0.41]		114-12004	
4 PLC ± -		WEIGHT 0.000000	
MATERIAL -		FINISH -	
		SIZE A2	CAGE CODE 00779
		DRAWING NO C=1484794	
		RESTRICTED TO -	
		CUSTOMER DRAWING	
		SCALE 2:1	SHEET 1 of 1
		REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1484794-1](#)