




- △ HOUSING MATERIAL: HIGH TEMPERATURE, GLASS-FILLED POLYMER. COLOR: GRAY OR WHITE. CONTACT: PHOSPHOR BRONZE.
- △ CONTACT: DIN 41612 CLASS 2 IN CONTACT AREA, TIN LEAD ON POSTS.
- △ RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- △ PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO HOT-STAMPED THIS APPROXIMATE AREA.
- △ CONTACT POINT.
- △ HOT-STAMPING ON THIS SIDE.

1 THRU 16		X	-	X	32	148526-5			
POSITIONS LOADED		C	B	A	NO. OF LOADED POSITION	PART NUMBER			
		ROWS LOADED							
THIS DRAWING IS A CONTROLLED DOCUMENT.					DIN B.CARBO	05 APR 99	tyco Electronics	Tyco Electronics Corporation	
					CHK C.RICHARD	05 APR 99		Harrisburg, PA 17105-3608	
					APVD C.RICHARD	05 APR 99		NAME	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC		RECEPTACLE ASSEMBLY,		
		0 PLC ± -			1		EUROCARD, TYPE 1/2R, 32		
		1 PLC ± -			2		POSITION, HIGH TEMPERATURE		
		2 PLC ± 0.13 [.005]			3				
		3 PLC ± -			4				
		4 PLC ± -			APPLICATION SPEC				
		ANGLES ± -			WEIGHT		SIZE		CAGE CODE
MATERIAL		FINISH			—		DRAWING NO		RESTRICTED TO
					A1		00779 C-148526		—
CUSTOMER DRAWING					SCALE		4:1		SHEET 1 OF 1
					REV		A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[148526-5](#)