






LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B2	REVISED PER ECO-11-004587	11MAR11	RK	HMR





6-32 X .250 LONG UNDERCUT BDG. HD. SCREW, PART NO. 1523927-1. SWITCHES 1520228-1, 1520228-2, 1520228-3, 1-1520228-1, 2-1520228-3, 2-1520228-4, 6520228-1, 6520228-2, 6520228-3, 1-6520228-1, 2-6520228-3, 2-6520228-4: QTY OF 4, SHIPPED UNASSEMBLED. SWITCH 1-1520228-0, 1-6520228-0 ONLY: QTY OF 4, SHIPPED ASSEMBLED.





2-1520228-4/2-6520228-4	7360K8 T-PAK	15/32" THD LENGTH DIE CAST	.469	DPST
2-1520228-3/2-6520228-3	7360K7 T-PAK	11/32" THD LENGTH DIE CAST	.344	DPST
1-1520228-1/1-6520228-1	8910K219	15/32" THD LENGTH DIE CAST	.469	DPST
1-1520228-0/1-6520228-0	8910K205	11/32" THD LENGTH DIE CAST	.344	DPST
1520228-6/6520228-6	7362K4	15/32" THD LENGTH DIE CAST	.469	SPST WITH BUSSING
1520228-3/6520228-3	7360K7	11/32" THD LENGTH DIE CAST	.344	DPST
1520228-2/6520228-2	7359K3	15/32" THD LENGTH DIE CAST	.469	DPST
1520228-1/6520228-1	7359K2	11/32" THD LENGTH DIE CAST	.344	DPST
PART NO.	ARAB NO.	BUSHING / PLATE ASSY	A	DESCRIPTION

- 1 T-PAK - SWITCH AND HARDWARE INDIVIDUALLY PACKED IN PLASTIC BAGS BEFORE BEING PLACED IN A INTERMEDIATE BOX WHICH IS THEN PLACED IN A SHIPPING BOX. SEE TABLE.
- 2 P/N X-6520228-X IS ROHS COMPLIANT.
- 3 MOUNTING DIMENSIONS FOR REFERENCE ONLY.

90-345



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN — 26SEP02		 TE Connectivity				
DIMENSIONS: INCHES		CHK — APVD —						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME					
	0 PLC ± —		20 AMP 125V AC/DC, 10 AMP 250V AC/DC,					
	1 PLC ± —		1 1/2 HP 125V/250V AC/DC, ONE HOLE MOUNTING					
	2 PLC ± —		TOOL HANDLE TOGGLE SWITCH					
	3 PLC ± —							
4 PLC ± —		PRODUCT SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
ANGLES ± —		—		APPLICATION SPEC				
MATERIAL		FINISH		WEIGHT		A2 00779 C=1520228		—
—		—		CUSTOMER DRAWING		SCALE		NTS
						SHEET		1 of 4
								REV
								B2

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



- 1 T-PAK – SWITCH AND HARDWARE INDIVIDUALLY PACKED  
IN PLASTIC BAGS BEFORE BEING PLACED IN AN INTERMEDIATE  
BOX WHICH IS THEN PLACED IN A SHIPPING BOX. SEE TABLE.
- 2 P/N X-6520228-X IS ROHS COMPLIANT.
- 3 MOUNTING DIMENSIONS FOR REFERENCE ONLY.

1520228-7/6520228-7	8909K23	15/32" THD LENGTH DIE CAST	.469	DPST T-PAKED W/SPECIAL HARDWARE
1520228-4/6520228-4	7360K8	15/32" THD LENGTH DIE CAST	.469	DPST
PART NO.	ARAB NO.	BUSHING / PLATE ASSY	A	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W. HANSON 29APR93 CHK W. Leonard 02MAY93 APVD F. WESOLEK 03MAY93		 TE Connectivity	
DIMENSIONS: INCHES  		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME 20 AMP 125V AC/DC, 10 AMP 250V AC/DC, 1 1/2 HP 125V/250V AC/DC, ONE HOLE MOUNTING TOOL HANDLE TOGGLE SWITCH	
MATERIAL -		FINISH -		WEIGHT -	
		CUSTOMER DRAWING		SCALE 2:1 SHEET 2 of 4 REV B2	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

D

D

C




C

B

B



A

A





CAP NUT, PART NO. 1522128-1,  
QTY OF 2, SHIPPED UNASSEMBLED.

6-32 X .250 LONG  
UNDERCUT BDG. HD. SCREW,  
PART NO. 1523927-1.  
QTY OF 2 APPLIED THIS  
END ONLY, SHIPPED  
UNASSEMBLED.






- 1 T-PAK - SWITCH AND HARDWARE INDIVIDUALLY PACKED IN PLASTIC BAGS BEFORE BEING PLACED IN A INTERMEDIATE BOX WHICH IS THEN PLACED IN A SHIPPING BOX. SEE TABLE.
- 2 PLY-O-PAK - SWITCH AND HARDWARE INDIVIDUALLY PACKED IN PLASTIC BAGS BEFORE BEING PACKED LOOSE IN A SHIPPING BOX. SEE TABLE.
- 3 P/N X-6520228-X IS ROHS COMPLIANT.
- 4 MOUNTING DIMENSIONS FOR REFERENCE ONLY.

2-1520228-5/2-6520228-5	7361K5 T-PAK	15/32" THD LENGTH DIE CAST	.469	SPST
1520228-9/6520228-9	8910K191	15/32" THD LENGTH DIE CAST	.469	SPST (PLY-O-PAK)
1520228-5/6520228-5	7361K5	15/32" THD LENGTH DIE CAST	.469	SPST
PART NO.	ARAB NO.	BUSHING / PLATE ASSY	A	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SMITH 13DEC77	 TE Connectivity					
DIMENSIONS: INCHES		CHK R. GLENN 13DEC77						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD M.R. DUMMER 13DEC77	NAME 20 AMP 125V AC/DC, 10 AMP 250V AC/DC, 1 1/2 HP 125V/250V AC/DC, ONE HOLE MOUNTING TOOL HANDLE TOGGLE SWITCH					
		PRODUCT SPEC —	SIZE A2 CAGE CODE 00779 DRAWING NO C-1520228 RESTRICTED TO —					
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL —	FINISH —	CUSTOMER DRAWING				SCALE NTS	SHEET 3 of 4	REV B2

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		-	SEE SHEET 1	-	-	-



- 1 P/N X-6520228-X IS ROHS COMPLIANT.
- 2 MOUNTING DIMENSIONS FOR REFERENCE ONLY.

1520228-8/6520228-8	8910K12	15/32" THD LENGTH DIE CAST	.469	DPST
PART NO.	ARAB NO.	BUSHING / PLATE ASSY	A	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	250CT95	<div>TE Connectivity</div>		
		CHK	01NOV95			
<div>DIMENSIONS: INCHES</div> <div></div>		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 20 AMP 125V AC/DC, 10 AMP 250V AC/DC, 1 1/2 HP 125V/250V AC/DC, ONE HOLE MOUNTING TOOL HANDLE TOGGLE SWITCH		
MATERIAL		FINISH		APVD	09NOV95	RESTRICTED TO
				M.R.DUMMER		
-		-		PRODUCT SPEC	SIZE	
				-	A2 00779	
				APPLICATION SPEC	CAGE CODE	
				-	1520228	
				WEIGHT	DRAWING NO	
				-	1520228	
				CUSTOMER DRAWING		SCALE
						2:1
						SHEET
						4 of 4
						REV
						B2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8910K205](#)