






RECOMMENDED PC BOARD LAYOUT

8	7	3, 4	—	1.270	.900	9	1.300	1.380	20	5—1571422—1		
	2	3, 4	—	1.270	.900	9	1.300	1.380	20	1571422—1		
		ROW M	ROW N	E	D	C	B	A	NO. OF POSN	PART NO.		
FINISH		SELECT LOADING .280 HIGH POST										
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R BROWN	13DEC02	 TE Connectivity						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK J GESFORD	13DEC02							
		0 PLC ± —		APVD J GESFORD	13DEC02	NAME HEADER ASSY, MOD II, DOUBLE ROW, .100x.100 CL, .025 SQ, COMPLIANT PIN POSTS, FOR .093 NOMINAL AND THICKER BOARDS, SELECT LOAD						
		1 PLC ± —		PRODUCT SPEC								
		2 PLC ± —		APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
		3 PLC ± .005		—		—		—				
MATERIAL		4 PLC ± —		WEIGHT		A2		00779	C=1571422	—		
		FINISH		SEE TABLE		CUSTOMER DRAWING						
						SCALE		4:1	SHEET	1 of 1	REV	A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1571422-1](#)