



- 1 INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, BLACK, UL94V-0.
- 2 MACHINED CONTACT: BECU, PLATED WITH 20 μ " MIN. GOLD THK. OVER 30-100 μ " THK. NICKEL.
- 3 SLEEVE: COPPER, PLATED WITH 180-340 μ " THK. TIN (LEAD FREE) OVER 75-125 μ " THK. NICKEL.
- 4 PARTS ARE END-TO-END STACKABLE AND BREAKABLE TO CREATE VARIOUS POSITION SIZES.
- 5 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



TOLERANCE $\pm .002$ UNLESS
OTHERWISE NOTED

		2.000	20	2-1571994-0
6 OBSOLETE		1.900	19	1-1571994-9
		1.800	18	1-1571994-8
		1.700	17	1-1571994-7
		1.600	16	1-1571994-6
		1.500	15	1-1571994-5
		1.400	14	1-1571994-4
		1.300	13	1-1571994-3
		1.200	12	1-1571994-2
		1.100	11	1-1571994-1
		1.000	10	1-1571994-0
6	OBSOLETE	0.900	9	1-1571994-9
6 OBSOLETE		0.800	8	1-1571994-8
		0.700	7	1-1571994-7
		0.600	6	1-1571994-6
		0.500	5	1-1571994-5
		0.400	4	1-1571994-4
		0.300	3	1-1571994-3
		0.200	2	1-1571994-2
6	OBSOLETE	0.100	1	1-1571994-1
		DIM "A"	POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S VISVESWARA CHK K.WRIGHT		26APROS  TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		ASSEMBLY SOCKET (.510 SERIES. S.I.P)	
MATERIAL		FINISH		SIZE	CAGE CODE
				A2	00779
				DRAWING NO	
				C-1571994	
CUSTOMER DRAWING				SCALE	SHEET
				4:1	1 of 1
				REV	P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1571994-2](#)