



- 1 INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, BLACK, UL94V-0.
- 2 MACHINED CONTACT: BECU, PLATED WITH 80-200 μ " THK. TIN (LEAD FREE) OVER 75-100 μ " THK. COPPER.
- 3 SLEEVE: COPPER, PLATED WITH 180-340 μ " THK. TIN (LEAD FREE) OVER 75-125 μ " THK. NICKEL.
- 4 PARTS ARE END-TO-END STACKABLE AND BREAKABLE TO CREATE VARIOUS POSITION SIZES.
- 5 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

TOLERANCE $\pm .002$ UNLESS
OTHERWISE NOTED

		2.000	20	2-1571995-0
OBSOLETE 		1.900	19	1-1571995-9
		1.800	18	1-1571995-8
		1.700	17	1-1571995-7
		1.600	16	1-1571995-6
OBSOLETE 		1.500	15	1-1571995-5
		1.400	14	1-1571995-4
		1.300	13	1-1571995-3
		1.200	12	1-1571995-2
	OBSOLETE	1.100	11	1-1571995-1
		1.000	10	1-1571995-0
OBSOLETE 		0.900	9	1571995-9
		0.800	8	1571995-8
		0.700	7	1571995-7
		0.600	6	1571995-6
		0.500	5	1571995-5
		0.400	4	1571995-4
		0.300	3	1571995-3
		0.200	2	1571995-2
	OBSOLETE	0.100	1	1571995-1
		DIM "A"	POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S VISVESWARA 26APROS		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK K WRIGHT	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD - NAME	
MATERIAL		FINISH		PRODUCT SPEC -	
				APPLICATION SPEC -	
		WEIGHT -		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-1571995 -	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 of 1 REV 02	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1571995-0](#)