





- ① MATERIAL: HOUSING—NYLON, UL94V—2,
COLOR—YELLOW,
CONTACTS—0.25 [.010] THICK
COPPER ALLOY.
- ② CONTACT FINISH: 0.003 [.0001]
MINIMUM THICK TIN—LEAD OVER 0.00127
[.000050] MINIMUM THICK NICKEL OVER
ENTIRE CONTACT.
3. SOLDER TAIL MEETS AMP SOLDERABILITY
SPECIFICATION 109—11—2.
- ④ RIBS ON FOUR CORNERS OPTIONAL.
- ⑤ AMP LOGO AND MATERIAL ID MAY BE
LOCATED ON EITHER LONG SIDE OF PART.
- ⑥ SIZE, SHAPE OR STYLE OF THIS FEATURE
MAY VARY.
- ⑦ CONTACT FINISH: 0.003 [.0001]
MINIMUM THICK TIN OVER 0.00127
[.000050] MINIMUM THICK NICKEL OVER
ENTIRE CONTACT.



		1-1586120-1
SUPERSEDED BY 1-158620-1		1586120-1
	FINISH	PART NUMBER

METRIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1586120-1](#)