



## REVISIONS

| P | LTR | DESCRIPTION   | DATE      | DWN | APVD |
|---|-----|---------------|-----------|-----|------|
|   | B3  | ECO-13-000550 | 10JAN2013 | DS  | AT   |
|   | B3  | ECO-14-000116 | 27FEB2014 | DS  | AT   |
|   |     |               |           |     |      |
|   |     |               |           |     |      |




1 MATERIAL:  
TYPE: COPPER ALLOY

2 FINISH:  
UNDERPLATE TYPE: NICKEL  
TOP PLATE TYPE: TIN

3. PARTS MUST BE FREE OF BURRS, CRACKS, OR OTHER VISUAL IMPERFECTIONS THAT MAY AFFECT FIT FORM OR FUNCTION

4 NOTE DELETED

|           |      |      |             |           |
|-----------|------|------|-------------|-----------|
| 5.41      | 6.10 | 7.70 | SIZE C      | 1587829-3 |
| 4.76      | 5.41 | 7.00 | SIZE B      | 1587829-2 |
| 4.11      | 4.76 | 6.40 | SIZE A      | 1587829-1 |
| MIN       | MAX  | E    | DESCRIPTION | PART NO   |
| WIRE O.D. |      |      |             |           |

|                                                                                     |  |                               |  |                                                                                                      |                    |                         |                    |
|-------------------------------------------------------------------------------------|--|-------------------------------|--|------------------------------------------------------------------------------------------------------|--------------------|-------------------------|--------------------|
| DIMENSIONS:<br>mm                                                                   |  | DWN<br>D SIMPSON<br>01JUN2009 |  | MATERIAL                                                                                             |                    | FINISH                  |                    |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                           |  | CHK<br>A TYLER<br>01JUN2009   |  |  TE Connectivity |                    |                         |                    |
| 0 PLC ±-<br>1 PLC ±0.2<br>2 PLC ±0.10<br>3 PLC ±0.013<br>4 PLC ±0.0001<br>ANGLES ±- |  | PRODUCT SPEC<br>108-2394      |  | NAME<br>OUTER FERRULE,<br>HVA280                                                                     |                    |                         |                    |
|                                                                                     |  | APPLICATION SPEC<br>114-13259 |  | SIZE<br>A4                                                                                           | CAGE CODE<br>00779 | DRAWING NO<br>C-1587829 | RESTRICTED TO<br>- |
|  |  | WEIGHT<br>-                   |  | CUSTOMER DRAWING                                                                                     |                    |                         |                    |
|                                                                                     |  |                               |  | SCALE<br>4:1                                                                                         | SHEET<br>1         | OF<br>1                 | REV<br>B3          |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1587829-1](#)