

REVISIONS		DATE	APPROVED
REV	DESCRIPTION		
D122869	REDRAWN TO CAEDS	93/02/22	WS
E123765	ADDED ITEMS 5 AND 6	93/05/27	WS
F133869	FOUND NO 5 WAS QTY 3, P/N 35859-01797/10/06	12-5	

# CONSTRUCTION

CONTACT RATING RES 25A 115/200V 400HZ  
MOT 15A 115/200V 400HZ

COIL RATING 28VDC  
PICKUP 18V MAX HOT  
DROPOUT 7V MAX HOT

RATED DUTY CONTINUOUS

VIBRATION MIL-E-5272 PROC 1

MAX WEIGHT 7-1/2 OZ


ALTITUDE 80, 000 FT

TEMP RANGE -65°C TO +85°C

MIN OPER CYCLES 50, 000



SHOCK 25G

# HERMETICALLY SEAL



NOTE:

COIL TRANSIENT VOLTAGE  
LIMITED TO ± 42 VOLTS  
REFERENCED TO ZERO  
VOLTS



6 AR 54102-001	RED ENAMEL PAINT DOT/GLYPTOL		
5 2 39529-001	OVERLAY		
4 1 16043-038	PLATE-NAME		
3 1 17959-001	PLATE-WARNING		
2 1 34753-001	PLATE-WIRING DIAGRAM		
1 1 20473-080	CONTACTOR ASSY-PRIMARY		
FINO QTY	PART OR IDENTIFYING NO	MANUFACTURE OR DESCRIPTION	MATERIAL OR NOTE
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON			
2 PL DEC. 3 PL DEC. ANGLES			
± .03	± .010	± 1°	
MATERIAL			
DR BY RLS	97/11/06	HARTMAN ELECTRICAL MANUFACTURING MANSFIELD, OHIO	
CHK BY	97/06/06		
ENG BY	97/06/06		
MFG	97/06/06		
RELEASE		CONTACTOR - 3PST HERMETICALLY SEALED 093	
CONTR NO.			
CONT APPVL			
SIZE	CODE IDENT	DWG NO.	
C	74063	DH-14 CE	
SCALE	NONE		SHEET

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DH14CE](#)