


LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	APVD
			C	REV PER ECO-06-010636	05JAN07	TK SF



6. REFERENCE ELCON PART NUMBERS 512-51-01131, TYCO PN 1648239-1
512-51-01134, TYCO PN 1648239-2

5. FOR TERMINATION, USE THE FOLLOWING EQUIPMENT:
BENCH CRIMP TOOL - 84C-E031
INDENTOR DIE SET - 84C-E007
ASSEMBLY LOCATOR - 84C-E003

4. MATERIAL:
CROWN CONTACT - BERYLLIUM COPPER ALLOY.
SOCKET HOUSING - TELLURIUM COPPER ALLOY
INSULATOR - THERMOPLASTIC, UL 94 V-0, COLOR - SEE TABLE.

	TYCO PN	COLOR
	1648239-1	BLACK
OBSOLETE	1648239-2	RED

3. FINISH:
SOCKET HOUSING - SILVER PLATED.
CROWN CONTACT - GOLD PLATED.

2. ITEMS PROVIDED TO THIS SPECIFICATION SHALL BE IDENTIFIED
ON THE CONTAINER WITH THE FOLLOWING INFORMATION:
PART NUMBER AND DATE CODE OF MANUFACTURE.

1. PART NUMBER CHANGES AND/OR DESIGN CHANGES AFFECTING
ITEM INTERCHANGEABILITY REQUIRE PRIOR ELCON APPROVAL
AND AUTHORIZATION BY REVISION TO THIS DRAWING.

NOTES: UNLESS OTHERWISE SPECIFIED:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.C.CANT 03APR97	<div><div>tyco</div><div>Electronics</div></div> <div>Tyco Electronics Corporation Harrisburg, PA 17105-3608</div>			
DIMENSIONS: INCHES		CHK —				
		APVD D.CHAU 25FEB06	NAME JUMPER, CROWN SOCKET SIZE 4 RT ANGLE X 6 CRIMP BARREL PN: 512-51-01131/512-51-01134			
		PRODUCT SPEC —	SIZE A3			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC —	CAGE CODE 00779			
MATERIAL —		WEIGHT —	DRAWING NO C-1648239			
FINISH —		CUSTOMER DRAWING	RESTRICTED TO —			
		SCALE 1:1	SHEET 1 OF 1		REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1648239-1](#)