

D

D

C


C

B

B

A

A



- 1

FRONT & REAR INSULATOR: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.
CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.
- 2

PART TO BE MARKED WITH TE IDENTIFICATION, TE PART NO.
AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.
3.

THIS INSERT CONTAINS: 6 CAVITIES FOR SIZE 12 PIN CONTACTS
4.

THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

NON-ENV		GPRBN06SB	1738104-2
ENVIRONMENTAL		GPRBE06SB	1738104-1
REMARKS		DESCRIPTIVE PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS CHK K. HOGAN APVD K. HOGAN	10-30-09 10-30-09 10-30-09
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		± ± ±0.05 ± ± ± ±	
MATERIAL 1 -		PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING	
		NAME INSERT ASSEMBLY, SOCKET, ARRANGEMENT 06, KEY B, GPRB	
		SIZE A260779	
		CAGE CODE C-1738104	
		DRAWING NO 1738104	
		RESTRICTED TO -	
		SCALE 4:1	
		SHEET 1 OF 1	
		REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738104-2](#)