

D

D

C




C

B


B

A

A



MATING FACE



THIS PRODUCT HAS NOT COMPLETED
VALIDATION TESTING

1 FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948. CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194, REAR GROMMET & INTERFACIAL SEAL: FLUROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.

2 PART TO MARKED WITH TE IDENTIFICATION, TE PART NO. AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.

3. THIS INSERT CONTAINS: 30 CAVITIES FOR SIZE 20 PIN CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALl SA.

NON-ENV	GPRBN30PA	1738166-3
GROMMET ONLY	GPRBH30PA	1738166-2
ENVIRONMENTAL	GPRBE30PA	1738166-1
REMARKS	DESCRIPTIVE PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 3-29-10	<div> TE Connectivity</div>			
DIMENSIONS:		CHK K. HOGAN 3-29-10				
mm		APVD K. HOGAN 3-29-10	NAME			
		PRODUCT SPEC	INSERT ASSEMBLY, PIN, ARRANGEMENT 30, KEY A, GPRB			
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		-	A2	00779	C-1738166	-
		CUSTOMER DRAWING	SCALE	4:1	SHEET	1 OF 1
					REV	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738166-3](#)