


D


C

B


A



MATING FACE




27.00
26.96



22.4 REF

12.05
12.01



- 1

FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948. CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194, REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.
- 2

PART TO MARKED WITH TE IDENTIFICATION, TE PART NO. AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.
- 3

THIS INSERT CONTAINS: 40 CAVITIES FOR SIZE 22 PIN CONTACTS
- 4

THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

NON-ENV	GPRBN40PB	1738191-3
GROMMET ONLY	GPRBH40PB	1738191-2
ENVIRONMENTAL	GPRBE40PB	1738191-1
REMARKS	DESCRIPTIVE PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS CHK K. HOGAN APVD K. HOGAN	10-4-10 10-4-10 10-4-10	TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME INSERT ASSEMBLY, PIN, ARRANGEMENT 40, KEY B, GPRB			
		0 PLC ±- 1 PLC ±0.1 2 PLC ±0.05 3 PLC ±- 4 PLC ±- ANGLES ±1 FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A200779	
MATERIAL 		-		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 4:1		SHEET 1 OF 1	
						REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738191-2](#)