







SECTION A-A
SCHNITT A-A




SCALE 1:1 / M 1:1

-2 AS SHOWN
-2 WIE GEZEICHNET



SCALE 1:1 / M 1:1

-4 AS SHOWN
-4 WIE GEZEICHNET



SCALE 1:1 / M 1:1

-5 AS SHOWN
-5 WIE GEZEICHNET

LOC	DIST	REVISIONS						
		AENDERUNGEN						
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		BESCHREIBUNG						
		PROJECT NR.: EGGMN09142	F1	ITEM 7. NEW PACKAGING UNIT ADDED		17NOV2010	VP	AW
			F2	APPLICATION SPEC. CHANGED		17OCT2011	VP	MS
			F3	OBSOLETE THE PARTS		30JAN2018	Z.W	S.M

- 1 PIN HOUSING AND PINCH RING SEAL ASSY PREASSEMBLED WITH CABLE SCREW JOINT
CABLE SCREW JOINT SCREWED WITH 2-3 TURNS ON PIN HOUSING
- 2 PACKAGING : PREASSEMBLED CONNECTORS WITHOUT PACKAGING, FOR INTERNAL USE ONLY
- 3 PLASTIC BAG (ITEM NO. 6) AND CORRUGATED BOX (ITEM 7; 8) NOT SHOWN
- 4 FOR CABLE DIAMETER 5.5mm TO 7.8mm
- 5 FOR CABLE DIAMETER 4.5mm TO 5.5mm
- 6 IN THIS AREA A MOULD INJECTION POINT UP TO MAXIMUM HEIGHT OF 2mm IS ACCEPTABLE
- 7 PACKAGING : 200 PIECES PREASSEMBLED CONNECTORS PACKAGED IN 2 PLASTIC BAG (ITEM. 6) PER 100 PCS
AND THESE PACKAGED IN ONE CORRUGATED SHIPPING BOX.
- 1 STIFTGEHÄUSE UND KLEMMKORB-DICHTUNGS-BAUGRUPPE VORASSEMBLIERT MIT KABELVERSCHRAUBUNG
KABELVERSCHRAUBUNG MIT 2-3 UMDREHUNGEN AUF DAS STIFTGEHÄUSE AUFGESCHRAUBT.
- 2 VERPACKUNG: OHNE VERPACKUNG FÜR INTERNE VERWENDUNG ALS KOMPONENTE
- 3 KUNSTSTOFF-BEUTEL (ITEM NR. 6) UND KARTON (ITEM NR. 7; 8) NICHT DARGESTELLT
- 4 FÜR LEITUNGSDURCHMESSER 5.5mm BIS 7.8mm
- 5 FÜR LEITUNGSDURCHMESSER 4.5mm BIS 5.5mm
- 6 IN DIESEM BEREICH EIN ANSPRITZPUNKT BIS ZU EINER MAXIMALEN HÖHE VON 2mm ZULÄSSIG
- 7 VERPACKUNG: 200 STÜCK VORASSEMBLIERTE STECKVERBINDER IM 2 KUNSTSTOFF-BEUTEL (ITEM NR. 6) MIT JE 100 STÜCK.
DIESE IN VERSANDKARTON VERPACKT

OBSOLETE
OBSOLETE
OBSOLETE
OBSOLETE
OBSOLETE
OBSOLETE

7 4		7 5		2 5		2 4	
3-1740939-5 1200 PCS OF 1740939-5	3-1740939-4 1200 PCS OF 1740939-4	3-1740939-2 1200 PCS OF 1740939-2	2-1740939-2 1200 PCS OF 1740939-2	1-1740939-2 1200 PCS OF 1740939-2	1740939-5 1740939-4 1740939-2		
1/200	1/200	1/200	1/200	-	-	-	-
2/200	2/200	2/200	2/200	-	-	-	-
1	1	1	1	-	1	1	1
1	1	1	1	-	1	1	1
1	1	1	1	-	-	-	-
1	1	1	1	-	-	1	-
1	1	1	1	-	1	-	-
1	1	1	1	-	-	-	-
QUANTITY STÜCK				ITEM NO. POS:		DESCRIPTION BENENNUNG	

ORDER-NO.
BESTELL-NR.

7	CORRUGATED BOX FOR 200 PCS KARTON FÜR 200 TEILE	3	-	-
6	PLASTIC BAG KUNSTSTOFF-BEUTEL	3	LDPE	-
5	PINCH RING SEAL, ASSY KLEMMKORB DICHTUNG, BAUGRUPPE	1	PA - PP/EPDM	-
4	CABLE SCREW JOINT KABELVERSCHRAUBUNG	1	PBT	BLACK SCHWARZ
3	PIN HOUSING MINUS STIFTGEHÄUSE MINUS	1	PPE+PS	BLACK SCHWARZ
2	PIN HOUSING PLUS STIFTGEHÄUSE PLUS	1	PPE+PS	BLACK SCHWARZ
1	PIN HOUSING NEUTRAL STIFTGEHÄUSE NEUTRAL	1	PPE+PS	BLACK SCHWARZ
MATERIAL		SURFACE / COLOUR OBERFLÄCHE / FARBE		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. ACKERMANN 07MAY2010	TE Connectivity	
DIMENSIONS: MASSEINHEITEN: [mm]		CHK N. GEISTER 07MAY2010		
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		APVD A. WÖBER 07MAY2010	NAME PHOTOVOLTAIK PIN CONNECTOR 1 POS. PREASSEMBLED	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES/WINKEL ± FINISH/OBERFLÄCHE/FARBE		PRODUCT SPEC PRODUKTSPEZ. 108-18701 APPLICATION SPEC VERARBEITUNGSSPEZ. 114-18488-1		
MATERIAL		WEIGHT GEWICHT	SIZE A2	CAGE CODE 00779
-		-	DRAWING NO. ZEICHNUNGS-NR. C-1740939	RESTRICTED TO NUR FÜR
- RESTRICTED CUSTOMER		/KUNDENZEICHNUNG		SCALE MASSSTAB 2:1
		SHEET BLATT 1	OF VON 1	REV F3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1740939-5](#)