



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

| LOC | DIST | REVISIONS |     |                       |         |     |      |
|-----|------|-----------|-----|-----------------------|---------|-----|------|
| J   | —    | P         | LTR | DESCRIPTION           | DATE    | DWN | APVD |
|     |      |           | E1  | REVISED ECR-08-031766 | 08DEC08 | SF  | KB   |



1. MUST BE KEPT BETWEEN **-A-** AND 2  
2. TO BE MATED WITH PLUG HOUSING SMOOTHLY  
3. APPLIED TAB CONTACT; P/N 173633 AND 173645  
4. APPLIED PLUG HOUSING; P/N 173852 etc
1. **-A-** 面より2mmの範囲で測定  
2. 相手ハウジングと所定の機能を満足して嵌合できること  
3. 内装するタブコンタクトは型番173633、173645  
4. 嵌合相手ハウジング型番173852 他



|                                          |               |                     |
|------------------------------------------|---------------|---------------------|
| V-2                                      | 白<br>(WHITE)  | 1-174934-1          |
| HB                                       | 黄<br>(YELLOW) | 174934-7            |
|                                          | 灰<br>(GRAY)   | 174934-6            |
|                                          | 青<br>(BLUE)   | 174934-5            |
|                                          | 緑<br>(GREEN)  | 174934-4            |
|                                          | 黒<br>(BLACK)  | 174934-2            |
|                                          | 白<br>(WHITE)  | 174934-1            |
| 使用材料難燃グレード<br>(FLAMMABILITY OF MATERIAL) | 色<br>(COLOR)  | 型番<br>(PART NUMBER) |

THIS DRAWING IS A CONTROLLED DOCUMENT.

|                   |                                                                       |
|-------------------|-----------------------------------------------------------------------|
| DIMENSIONS:<br>mm | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                |
|                   | 0 PLC ±—<br>1 PLC ±—<br>2 PLC ±—<br>3 PLC ±—<br>4 PLC ±—<br>ANGLES ±— |
| MATERIAL<br>PBT   | FINISH<br>—                                                           |

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
一般公差  
10± : ±0.2  
30± > 10 : ±0.25  
> 30 : ±0.3  
ANGLE : ±3°

|                  |         |
|------------------|---------|
| DWN<br>S.FUJITA  | 08DEC08 |
| CHK<br>K.BETSUI  | 08DEC08 |
| APVD<br>K.BETSUI | 08DEC08 |
| PRODUCT SPEC     | —       |
| APPLICATION SPEC | —       |
| WEIGHT           | —       |

CUSTOMER DRAWING

Tyco Electronics Corporation  
Kawasaki, Japan

070 SERIES MULTILOCK I/O CONNECTOR  
14POSITION CAP HOUSING WIRE TO WIRE

|              |                    |                        |                    |
|--------------|--------------------|------------------------|--------------------|
| SIZE<br>A3   | CAGE CODE<br>00779 | DRAWING NO<br>C-174934 | RESTRICTED TO<br>— |
| SCALE<br>2:1 |                    |                        | SHEET<br>1 OF 1    |
| REV<br>E1    |                    |                        |                    |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[174934-2](#)