


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED	ECR-17-015588	24OCT2017	TS HY



D



C

B

A



- 1 -A- 面より2mmの範囲で測定。
2 相手ハウジングと所定の機能を満足して嵌合できること。
3. 内装するタブコンタクト型番；173633, 173645
4. 嵌合相手ハウジング型番；173851, 173853
- 1 MUST BE KEPT BETWEEN -A- AND 2.
2 TO BE MATED WITH THE PLUG HOUSING SMOOTHLY.
3. APPLIED TAB CONTACT PART NUMBER；173633, 173645
4. APPLIED PLUG HOUSING PART NUMBER；173851, 173853

D

C

B

A

TOLERANCE UNLESS OTHERWISE SPECIFIED:	
一般公差	
0 < x ≤ 10	: ±0.2
10 < x ≤ 30	: ±0.25
30 < x ≤ 100	: ±0.3
ANGLE	: ±3°
角度	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.SUZUKI 3/29'89		 TE Connectivity						
DIMENSIONS:		CHK T.SAGAWA 3/30'89								
mm		APVD S.ISOHATA 7/4'89		NAME 070 SERIES MULTI-LOCK CONNECTOR 30POSITION CAP HOUSING (W-W)						
		PRODUCT SPEC —								
		APPLICATION SPEC —								
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
PBT		—		WEIGHT 19.8 g	A2	00779	C=174939		—	
CUSTOMER DRAWING						SCALE	2:1	SHEET	1 of 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-174939-1](#)