





NUMBER
C-176204



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST



NOTE:
1. MUST BE KEPT BETWEEN -Z- AND 2mm
2. THE MATING CAP HSG PART NUMBER; 176206
3. APPLIED CONTACT; P/N 173716, 173630, 173631

注:
1. -Z- 面より 2mm の範囲で測定
2. 嵌合相手ハウジング型番: 176206
3. 内装するリセブタクルコンタクト型番は 173716, 173630, 173631

灰色 (LIGHT GRAY)	6-176204-6
白色 (WHITE)	176204-1
色 (COLOR)	PART NUMBER

				Copyright ©1989年 AMP (Japan), LTD. 東京エー・エム・ピー株式会社				Copyright ©1989 AMP (Japan), LTD. ALL RIGHTS RESERVED.				AMP (JAPAN), LTD. Tokyo, Japan																			
				WIRE RANGE —H— mm CANG -)				INSULATION DIA —H— mm				NAME 26極 プラグ ハウジング .040/.070シリーズ ハイブリッド I/O コネクタ 26pos.PLUG HOUSING .040/.070SERIES HYBRID I/O CONN.																			
C 追加 J-0186 AMP				B 変更 J-12805 Y.FK.Y				A 変更 J-10838 T.S.K.A				O 作成 K.SY.M				DR. 6/19/89 K. Sasaki				DE 6/19/89 T. Sasaki				GENERAL TOLERANCE 0mm 10 : ±0.2 10mm 30 : ±0.25 30mm 100 : ±0.3 ANGLES : ±3°				LOC B J		NUMBER C-176204	
LTR REVISION RECORD				DR CHK DATE				MATERIAL PBT				FINISH ---				CHK. 6/20/89 M. Matsuda				APP. -				SCALE 2-1		REV. C		SHEET —H—			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[176204-1](#)