






UNIT A:  
P1: WHITE-GREEN  
P2: WHITE-GREEN  
P3: WHITE-GREEN  
P4: WHITE-GREEN  
UNIT B:  
P5: YELLOW-ORANGE  
UNIT C:  
6. RED  
7. VIOLET  
8. WHITE  
9. GREEN  
10. BLUE



| CONNECTION TABLE |      |            |       |       |
|------------------|------|------------|-------|-------|
| CABLE            |      |            | HDMI  | DVI   |
| CONSTRUCTION     | UNIT | WIRE COLOR | PIN   | PIN   |
| STP<br>(BROWN)   | A    | GREEN      | 1     | 2     |
|                  |      | DRAIN WIRE | 2     | 3     |
|                  |      | WHITE      | 3     | 1     |
| STP<br>(RED)     | A    | GREEN      | 4     | 10    |
|                  |      | DRAIN WIRE | 5     | 11    |
|                  |      | WHITE      | 6     | 9     |
| STP<br>(GREEN)   | A    | GREEN      | 7     | 18    |
|                  |      | DRAIN WIRE | 8     | 19    |
|                  |      | WHITE      | 9     | 17    |
| STP<br>(BLUE)    | A    | GREEN      | 10    | 23    |
|                  |      | DRAIN WIRE | 11    | 22    |
|                  |      | WHITE      | 12    | 24    |
| —                |      |            | 13    | NC    |
| —                |      |            | 14    | NC    |
| SINGLE WIRE      | C    | WHITE      | 15    | 6     |
| SINGLE WIRE      | C    | GREEN      | 16    | 7     |
| TWIST PAIR       | B    | YELLOW     | 17    | 15    |
|                  |      | ORANGE     | 18    | 14    |
| SINGLE WIRE      | C    | BLUE       | 19    | 16    |
| —                |      |            | NC    | 8     |
| SHIELD BRAID     |      |            | SHELL | SHELL |

|           |           |
|-----------|-----------|
| 1770020-7 | 1500±20   |
| 1770020-6 | 1000±20   |
| 1770020-5 | 750±10    |
| 1770020-4 | 500±10    |
| 1770020-3 | 250±10    |
| 1770020-2 | 3000±30   |
| 1770020-1 | 2000±20   |
| P/N       | LENGTH(A) |

|      |     |                                                                                           |          |
|------|-----|-------------------------------------------------------------------------------------------|----------|
| A/R  | MR  | HEAT SHRINK TUBING, ID=1.5MM, BLUE                                                        | 17       |
| A/R  | MR  | HEAT SHRINK TUBING, ID=1.5MM, BROWN                                                       | 16       |
| A/R  | MR  | HEAT SHRINK TUBING, ID=1.5MM, GREEN                                                       | 15       |
| A/R  | MR  | UL TAPE, W=9MM                                                                            | 14       |
| A/R  | KG  | PVC, BLACK, 95±3 SHORE A                                                                  | 13       |
| 1    | PC  | SHELL, FOR HDMI                                                                           | 12       |
| A/R  | MR  | HEAT SHRINK TUBING, ID=1.5MM, RED                                                         | 11       |
| A/R  | MR  | ACETATE TAPE, COLOR: BLACK, T=0.22MM, W=10MM, L=50MM                                      | 10       |
| A/R  | MR  | HEAT SHRINK TUBING, ID: 2.5MM, BLACK.                                                     | 9        |
| A/R  | MR  | HEAT SHRINK TUBING, ID: 0.7MM, BLACK.                                                     | 8        |
| 2    | PC  | SCREW, DVI #4-40 L=45MM                                                                   | 7        |
| 1    | PC  | METAL CAN FOR DVI CONN.                                                                   | 6        |
| 1    | PC  | DVI-D DIGITAL, 18PIN+1PIN, GOLD FLASH                                                     | 5        |
| A/R  | KG  | PVC, 40P, COLOR: BLACK                                                                    | 4        |
| A/R  | MR  | HEAT SHRINK TUBING, ID: 1.0MM, BLACK.                                                     | 3        |
| 1    | PC  | HDMI 19PIN PLUG                                                                           | 2        |
| A/R  | MR  | CABLE, UL20276 (1P*30AWG+DRAIN+AL/MYLAR)*4+30AWG*1P+28AWG*5C+AL/MYLAR+BRAID, COLOR: BLACK | 1        |
| Q'TY | U/M | DESCRIPTION                                                                               | ITEM NO. |

LDC  
HY  
DIST

|     |                           |         |     |      |
|-----|---------------------------|---------|-----|------|
| E1  | REVISED PER ECO-11-005027 | 19APR11 | RK  | HMR  |
| LTR | REVISION RECORD           | DATE    | DWN | APVE |

|                |  |                                       |  |          |         |                 |        |                       |  |
|----------------|--|---------------------------------------|--|----------|---------|-----------------|--------|-----------------------|--|
| DIMENSIONS: MM |  | TOLERANCES UNLESS OTHERWISE SPECIFIED |  | SIZE A3  | SCALE — | SHEET 1 OF 1    | REV E1 | TE CONNECTIVITY       |  |
| 0 PLC ±        |  | —                                     |  | DWN      | M.TSAI  | ENG. J.PI       |        | NAME                  |  |
| 1 PLC ±        |  | —                                     |  | CHK      | J.PI    | CHK             |        | CABLE ASSY, DVI-HDMI  |  |
| 2 PLC ±        |  | —                                     |  | APVD     |         | J.CHEN          |        | DRAWING NO. C-1770020 |  |
| 3 PLC ±        |  | —                                     |  | ANGLES ± |         | SURFACE TEXTURE |        | CUSTOMER DRAWING      |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1770020-5](#)