

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	CUTTING BURR DETAILS ADDED	19NOV2018	RK	PS


1. MATERIAL:
HOUSING: POLYAMIDE 6/6, UL94V-0.
COLOR: BROWN.
TUBULAR CONTACT: TIN PLATED, BRASS.
SCREW: M3.5 STEEL, ZINC PLATED W/ NON-
HEXAVALENT CHROMATE (CHROME III).
WIRE PROTECTOR: STAINLESS STEEL.

2. CURRENT RATING: 40A.
OPERATING VOLTAGE: 250V.
WIRE RANGE: 10-24 AWG.

3. CONTINUOUS WORKING TEMP.: -50°C TO +160°C.

- △ CUTTING PROJECTION CAN BE ON BOTH SIDES
DEPENDING ON CUTTING LOCATION.


5. CUTTING BURR MAX. 1mm ALLOWED.



1776304-4 AS SHOWN

OBSOLETE

120.0	139.5	12	TSB100012DSHT	1-1776304-2
108.0	127.5	11	TSB100011DSHT	1-1776304-1
96.0	115.5	10	TSB100010DSHT	1-1776304-0
84.0	103.5	9	TSB100009DSHT	1776304-9
72.0	91.5	8	TSB100008DSHT	1776304-8
60.0	79.5	7	TSB100007DSHT	1776304-7
48.0	67.5	6	TSB100006DSHT	1776304-6
36.0	55.5	5	TSB100005DSHT	1776304-5
24.0	43.5	4	TSB100004DSHT	1776304-4
12.0	31.5	3	TSB100003DSHT	1776304-3
—	19.5	2	TSB100002DSHT	1776304-2
—	7.5	1	TSB100001DSHT	1776304-1
DIM B	DIM A	NO. OF POS.	CATALOG NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 3/21/05	TE Connectivity Ltd.				
DIMENSIONS: mm		CHK C RICHARD 3/21/05					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C RICHARD 3/21/05	NAME 12mm PITCH, EUROPA TERMINAL BLOCK HIGH TEMP. —				
	0 PLC ± — 1 PLC ± 0.7 2 PLC ± 0.25 3 PLC ± — 4 PLC ± — ANGLES ± 2°	PRODUCT SPEC —					
		APPLICATION SPEC —					
		WEIGHT —					
MATERIAL SEE NOTES	FINISH SEE NOTES		SIZE A3	CAGE CODE 00779	DRAWING NO C=1776304	RESTRICTED TO —	
CUSTOMER DRAWING					SCALE NTS	SHEET 1 OF 1	REV A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TSB100004DSHT](#) [TSB23003DS](#) [TSB23006DS](#) [TSB100001DS](#) [TSB23008DS](#) [TSB23012DS](#) [TSB23010DS](#)