






8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.			
PART NUMBER		REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION	
1852537-1		A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER	
1852537-2		A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER	
1852537-3		A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER	
1852537-6		A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER	
7-1852537-7		A	-	-	-	SPARE PARTS	

- △ RECOMMENDED SPARE PARTS
△ GREASE LIGHTLY
△ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE




AMP-O-LECTRIC TERM GUARD



G TERMINATOR GUARD

TERMINAL NAME: .070 MALE TERMINAL					
TE PN	MANF PN	MOLEX TERMINAL - TE CRIMP SPECS			
1949467	35747-0210	PAD LTR	CRIMP HEIGHT		WIRE SIZE
1949509	35748-0210	A	1.73±0.05mm[.068±.002]		14 AWG
1949510	35746-0210	B	1.52±0.05mm[.060±.002]		16AWG
1949441	35745-0210	C	1.42±0.05mm[.056±.002]		18AWG
-	-	D	±.002[±0.05mm]		-
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	2.29mm [.090]	F	14-18 AWG
-	-	INSUL	3.56mm [1.40]	F	3.8mm MAX
WIRE STRIP LENGTH 3.91-4.28mm		TERM APPL SPEC NONE	FEED 11.99mm	APPLICATOR INSTRUCTIONS 408-8040	SET UP GAGE 458637-1



-	2	2	2	2	-	1-354779-4	PIN, WIRE DISC, .3060	128
-	2	2	2	2	-	354779-6	PIN, WIRE DISC, .3020	127
-	2	2	2	2	-	8-354778-8	PIN, WIRE DISC, .2935	126
△	-	-	REF	-	..	455749-1	GUARD WINDOW	116
△	-	-	REF	-	..	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	2	2	2	2	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	53
-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
-	1	1	1	1	-	690753-1	SPACER, TONKER	50
-	-	-	-	-	..	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	-	-	..	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	1	-	690501-4	CAM, POST FEED, 1 5/8	47
-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MOCA)	46
-	1	1	1	1	-	690191-1	PLUG,NYLON	45
-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	690124-1	WASHER, RAM (.115)	42
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	690142-1	DISC, INSULATION	38
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	690212-1	POST, RAM	35
-	1	1	1	1	-	690786-3	TERMINAL SUPPORT	34
-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	1320908-1	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	1633091-1	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
-	1	1	1	1	-	1320928-1	PLATE, STRIP GUIDE	24
-	1	-	-	1	-	690472-2	STRIPPER	22
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	1	1	-	-	691353-1	STRIPPER	19
△	-	1	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	13
△	-	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
△	-	1	1	1	-	690461-1	STOP, SHEAR	11
△	-	-	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
△	-	1	1	1	-	454276-1	FLOATING SHEAR, FRONT	9
△	1	1	1	1	-	2-1633110-1	ANVIL, COMBINATION .090	8
-	-	-	-	-	..	-	-	7
-	-	-	-	-	..	-	-	6
-	1	1	1	1	-	1-455889-4	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	238011-4	BLOCK, CRIMPER SPACER	4
△	1	1	1	1	-	3-683453-1	CRIMPER, INSULATION PREMIUM	3
△	-	1	1	1	-	455888	SPACER, CRIMPER	2
△	1	1	1	1	-	3-456406-3	CRIMPER, WIRE PREMIUM	1

THIS IS A CUSTOMER DRAWING. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED FOR THE CUSTOMER'S DESIGN AND CONSTRUCTION ONLY. IT IS NOT TO BE REPRODUCED OR USED FOR ANY OTHER PURPOSE WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS CORPORATION. THE CUSTOMER SHALL BE RESPONSIBLE FOR THE PROTECTION OF THIS DRAWING.		DRAWN C. REICHELDERFER 30AUG2007	Tyco Electronics Harrisburg, PA 17105-3608		
DIMENSIONS: INCHES		APPROVED T. ELBIN 30AUG2007	NAME SIDE FEED HDM APPLICATOR		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
9 PLC ±.01		APPLICATION SPEC			
1 PLC ±.01		WEIGHT			
2 PLC ±.01		CUSTOMER DRAWING			
3 PLC ±.001		SCALE 3:5			
4 PLC ±.0001		SHEET 1 OF 1			
ANGLES ±.0001		REV A			
FINISH					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852537-6](#)