







8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER		REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION	
1852698-1		A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER	
1852698-2		A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER	
1852698-3		A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER	
1852698-6		A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER	
7-1852698-7		A	-	-	-	SPARE PARTS	


- △ RECOMMENDED SPARE PARTS
△ GREASE LIGHTLY
△ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE




AMP-O-LECTRIC TERM GUARD

G TERMINATOR GUARD

TERMINAL NAME: 3032 SERIES TERMINAL					
TE PN	MANUF PN	CONEXCON TERMINAL - TE CRIMP SPECS			
1949686	3032-2000				
-	-	PAD LTR	CRIMP HEIGHT	WIRE SIZE	
-	-	A	1.17mm+.05/- .05 [.046+.002/- .002]	18AWG	
-	-	B	1.05mm+.05/- .05 [.041+.002/- .002]	20AWG	
-	-	C	.95mm+.05/- .05 [.038+.002/- .002]	22AWG	
-	-	D			
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	1.68mm [.066]	F	22-18 AWG
-	-	INSUL	2.54mm [.100]	F	Ø2.700 MAX
WIRE STRIP LENGTH 2.858-3.239	TERM APPL SPEC NONE	FEED 8.712	APPLICATOR INSTRUCTIONS 408-8040		SET UP GAGE 458637-1



-	2	2	2	2	-	3-354779-6	PIN, WIRE DISC, .3170	128
-	2	2	2	2	-	2-354779-7	PIN, WIRE DISC, .3125	127
-	2	2	2	2	-	1-354779-8	PIN, WIRE DISC, .3080	126
△	-	-	REF	-	..	455749-1	GUARD WINDOW	116
△	-	-	REF	-	..	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	455888-3	SPACER, CRIMPER	82
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 X .25	62
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	-	-	-	-	..	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	-	-	..	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	1	-	690501-4	CAM, POST FEED, 1 5/8	47
-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MOCA)	46
-	1	1	1	1	-	690191-1	PLUG,NYLON	45
-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	1-690124-4	WASHER, RAM (.120)	42
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	690142-1	DISC, INSULATION	38
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	690212-1	POST, RAM	35
-	1	1	1	1	-	690786-1	TERMINAL SUPPORT	34
-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	1320908-2	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	1633091-1	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
-	1	1	1	1	-	1320928-2	PLATE, STRIP GUIDE	24
-	1	-	-	1	-	690472-2	STRIPPER	22
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	2	2	2	2	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	1	1	-	-	691353-1	STRIPPER	19
△	-	1	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	13
△	-	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
△	-	1	1	1	-	690461-1	STOP, SHEAR	11
△	-	-	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
△	-	1	1	1	-	462006-1	FLOATING SHEAR, FRONT	9
△	1	1	1	1	-	7-1633535-6	ANVIL, COMBINATION	8
-	-	-	-	-	..	-	-	7
-	-	-	-	-	..	-	-	6
-	1	1	1	1	-	2-455889-0	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	1-238011-0	BLOCK, CRIMPER SPACER	4
△	1	1	1	1	-	4-456134-5	CRIMPER, INSULATION F PREMIUM	3
△	-	1	1	1	-	455888-6	SPACER, CRIMPER	2
△	1	1	1	1	-	2-1633588-6	CRIMPER, WIRE	1

-77 -6 -3 -2 -1 U/M				PART NO				DESCRIPTION				ITEM NO		
THIS DRAWING IS A CONTROLLED DOCUMENT FOR ENDO-ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE WITHOUT NOTICE AND THE USER SHALL BE RESPONSIBLE FOR VERIFYING THE LATEST VERSION.														
DIMENSIONS: INCHES 				TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.01 1 PLC ±.01 2 PLC ±.01 3 PLC ±.01 4 PLC ±.0001 ANGLES ±.0001				DWG M. HERR 13MAY2008		 Tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608				
								CHK G. BAILEY 13MAY2008						
MATERIAL -				FINISH -				APVD W. DEMING 13MAY2008		NAME SIDE FEED HDM APPLICATOR				
								APPLICATION SPEC -		-				
CUSTOMER DRAWING				WEIGHT -				SIZE A1		CAGE CODE 00779		DRAWING NO C=1852698		RESTRICTED TO -
								SCALE 3:5		SHEET 1		OF 1	REV A	

CUSTOMER VIEWABLE ASSEMBLY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852698-2](#)