




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT -

ALL RIGHTS RESERVED.


REFERENCE MATING INTERFACE PATTERN:
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.



SCALE 3:1



SOLDER DETAIL
SCALE 10:1




EXAMPLE SOLDER JOINT

NOTES:


- 1 TAPE FOR VACUUM P&P ONLY FOR DASHNUMBERS 7- /8- /9-
- 2 FOR PACKAGING SEE SHEET 2 OF 2
- 3 WITHOUT VACUUM TAPE.
- 4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY.
SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
- 5 SHOWN IS A 10 POSITION CONNECTOR.

LOC		DIST		REVISIONS					
H		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					S4	PACKAGING BLISTER MATERIAL CHANGE	08MAY2015	NV	PS

PART NUMBER VAC. TAPE. 1	PART REV	PART NUMBER 3	PART REV	NR.OF POS. "n"	"A"	"B" MAX.
7-188275-4	U	0-188275-4	U	4	3,81	7,1
7-188275-6	U	0-188275-6	U	6	6,35	9,7
7-188275-8	U	0-188275-8	U	8	8,89	12,2
8-188275-0	U	1-188275-0	U	10	11,43	14,7
8-188275-2	U	1-188275-2	U	12	13,97	17,3
8-188275-4	U	1-188275-4	U	14	16,51	19,8
8-188275-6	U	1-188275-6	U	16	19,05	22,4
8-188275-8	V	1-188275-8	V	18	21,59	24,9
9-188275-0	U	2-188275-0	U	20	24,13	27,5



ACCORDING EIA-481/DIN IEC 286



POLARIZATION-SLOT
ON THIS SIDE.

3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	RED
1	FEMALE CONTACT	PHOSPHOR BRONZE	TIN OVER NICKEL
ITEM NO.	COMPONENT DESCRIPTION	MATERIAL	FINISH / COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.GOSSELINK	-
		CHK -	-
		APVD -	-
		PRODUCT SPEC 108-19052	-
		APPLICATION SPEC 114-13318	-
		WEIGHT -	-
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 2

TE Connectivity		CONNECTOR, FEMALE-ON-BOARD TOP-ENTRY, SMD, Micro-MaTch	
SIZE A3	CAGE CODE 00779	DRAWING NO C-188275	RESTRICTED TO -
		SCALE 5:1	SHEET 1 OF 2
		REV S4	

RECOMMENDED PC-BOARD
PAD-LAYOUT TOP VIEW

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD





SEE SHEET 1

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm



7-188275-4

7-188275-6

7-188275-8

8-188275-0

4 POSITION

6 POSITION

8 POSITION





10 POSITION

0-188275-4

0-188275-6

0-188275-8

1-188275-0








TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm



8-188275-2

8-188275-4

8-188275-6

8-188275-8

9-188275-0

12 POSITION

14 POSITION

16 POSITION

18 POSITION

20 POSITION






1-188275-2

1-188275-4

1-188275-6

1-188275-8

2-188275-0



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

M. GOSSELINK

CHK

-

APVD

-

PRODUCT SPEC

108-19052

APPLICATION SPEC

114-13318


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±-

1 PLC

±0.1

2 PLC

±0.05

3 PLC

±-

4 PLC

±-

ANGLES

±-

FINISH

-

MATERIAL

-



TE Connectivity

CONNECTOR,
FEMALE-ON-BOARD TOP-ENTRY,
SMD, Micro-MaTch

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-188275

RESTRICTED TO

-

SCALE

1:1

SHEET

2

OF

2

REV

S4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-188275-0](#)