






THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -


ALL RIGHTS RESERVED.

REFERENCE MATING INTERFACE PATTERN:——
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.




NOTES:

- 1 TAPE FOR VACUUM P&P ONLY FOR DASHNUMBERS 7- /8- /9-
2 FOR PACKAGING SEE SHEET 2 OF 2
3 WITHOUT VACUUM TAPE.
4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY.
SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
5 SHOWN IS A 10 POSITION CONNECTOR.



—ACCORDING EIA-481/DIN IEC 286



3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	RED
1	FEMALE CONTACT	PHOSPHOR BRONZE	TIN OVER NICKEL
ITEM NO.	COMPONENT DESCRIPTION	MATERIAL	FINISH / COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.				ITEM NO.		CONNECTION SECURITY POSITION		DATE REVISION		PART NUMBER & COLOR											
				DWN		-		TE Connectivity													
				M. GOSSELINK		-															
				CHK		-		NAME													
				-		-															
DIMENSIONS:				TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD													
mm								-		CONNECTOR, FEMALE-ON-BOARD TOP-ENTRY, SMD, Micro-MatCh											
				PRODUCT SPEC																	
				108-19052																	
				APPLICATION SPEC																	
				114-13318																	
MATERIAL				FINISH				SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO							
SEE TABLE				SEE TABLE				A3		00779		©=188275		-							
CUSTOMER DRAWING										SCALE		5.1		SHEET		1 OF 2		REV		S4	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD





SEE SHEET 1

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm



7-188275-4

7-188275-6

7-188275-8

8-188275-0

4 POSITION

6 POSITION

8 POSITION





10 POSITION

0-188275-4

0-188275-6

0-188275-8

1-188275-0








TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm



8-188275-2

8-188275-4

8-188275-6

8-188275-8

9-188275-0

12 POSITION

14 POSITION

16 POSITION

18 POSITION

20 POSITION






1-188275-2

1-188275-4

1-188275-6

1-188275-8

2-188275-0



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

M. GOSSELINK

CHK

-

APVD

-

PRODUCT SPEC

108-19052

APPLICATION SPEC

114-13318


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±-

1 PLC

±0.1

2 PLC

±0.05

3 PLC

±-

4 PLC

±-

ANGLES

±-

FINISH

-

MATERIAL

-



TE Connectivity

CONNECTOR,
FEMALE-ON-BOARD TOP-ENTRY,
SMD, Micro-MaTch

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

©-188275

-

SCALE

1:1

SHEET

2

OF

2

REV

S4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-188275-8](#)