


Restricted to: General Release


USED ON

THIS DRAWING IS A CONTROLLED DOCUMENT



**Left Side**

Connector(s): MT-RJ (No Pins)  
 Mode: MM  
 Housing Color: Black  
 Geom. Spec: 115-1215



**Fiber Path**

Fiber A - - B  
 Fiber B - - A

**Right Side**

Connector(s): LC-Duplex Secure  
 Mode: MM  
 Housing Color: Blue  
 Geom. Spec: N/A

**Notes:**

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS THE PROPERTY OF TYCO ELECTRONICS, INC. AND IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC  
 CE  
 DIST  
 16

A	Rev Per	EC#	RELEASE	2/15/2006	-	DF	
P	LTR		REVISION RECORD	DATE	DIN	APVD	

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	0 PLC ± .
	1 PLC ± .
	2 PLC ± .
	3 PLC ± .
	4 PLC ± .

DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	-
CHK	Dave Fennell	Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Dave Fennell				
NAME	FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1907125
SHEET	1 of 4	REV	A		

Customer Print

Restricted to: General Release

USED ON

THIS DRAWING IS A CONTROLLED DOCUMENT.

Part #	L (meters)	L (feet)	MT-RJ (No Pins), Black		LC-Duplex Secure, Blue	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1907125-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-1907125-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-1907125-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-1907125-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-1907125-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-1907125-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	-
0-1907125-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	-
0-1907125-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	-
0-1907125-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-1907125-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-1907125-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	-
1-1907125-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-1907125-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	-
1-1907125-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	-
1-1907125-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	-
1-1907125-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	-
1-1907125-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-1907125-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	-
1-1907125-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	-
2-1907125-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-1907125-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	-
2-1907125-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	-
2-1907125-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	-
2-1907125-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	-
2-1907125-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	-
2-1907125-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	-
2-1907125-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	-
2-1907125-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	-
2-1907125-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	-
3-1907125-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	-
3-1907125-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	-
3-1907125-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	-
3-1907125-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	-
3-1907125-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	-
3-1907125-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	-
3-1907125-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	-
3-1907125-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	-
3-1907125-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	-
3-1907125-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	-
4-1907125-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	-
4-1907125-1	40.590 - 41.410	133.16 - 135.85	0.56	20	0.56	-
4-1907125-2	41.580 - 42.420	136.41 - 139.17	0.56	20	0.56	-

Qty	U of M	Description	Item No.
1	piece	LC Duplex clip, black	14
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	13
1	piece	PIN KEEPER, 3.8MM	12
AR	meter	2 fiber, 62.5/125, 1.8 mm, Twinzip, Orange, OFNR (Riser)	11
2	piece	Trace Label	10
1	piece	CRIMP EYELET, MT-RJ	9
1	piece	HOUSING, CONN, MT-RJ.BLACK	8
1	piece	SPRING, MT-RJ, 3.8 DESIGN	7
2	piece	LC, SC, FC Straight Boot, Beige	6
2	piece	Eyelet/Shrink tube assembly - White	5
1	piece	DUST COVER, MT-RJ	4
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	3
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	2
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS TO BE KEPT CONFIDENTIAL AND NOT TO BE DISCLOSED TO ANY OTHER PERSONS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

LOC CE DIST 16

Rev Per EC#	RELEASE	2/15/2006	-	DF
P LTR	REVISION RECORD	DATE	DIN	APVD

Customer Print

DIN Cable Assy Configurator	MATERIAL -	HEAT TREAT -
OK Dave Fennell		
APVD Dave Fennell		
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure		
SCALE NTS	SIZE A2	DRAWING NO C- 1907125
SHEET 2 of 4	REV A	

8 7 6 5 4 3 2 1

Restricted to: General Release

Part #	L (meters)	L (feet)	MT-RJ (No Pins), Black		LC-Duplex Secure, Blue	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1907125-3	42.570 - 43.430	139.66 - 142.48	0.56	20	0.56	-
4-1907125-4	43.560 - 44.440	142.91 - 145.80	0.57	20	0.57	-
4-1907125-5	44.550 - 45.450	146.16 - 149.11	0.57	20	0.57	-
4-1907125-6	45.540 - 46.460	149.40 - 152.42	0.57	20	0.57	-
4-1907125-7	46.530 - 47.470	152.65 - 155.74	0.57	20	0.57	-
4-1907125-8	47.520 - 48.480	155.90 - 159.05	0.57	20	0.57	-
4-1907125-9	48.510 - 49.490	159.15 - 162.36	0.57	20	0.57	-
5-1907125-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-
5-1907125-1	50.490 - 51.510	165.64 - 168.99	0.58	20	0.58	-
5-1907125-2	51.480 - 52.520	168.89 - 172.30	0.58	20	0.58	-
5-1907125-3	52.470 - 53.530	172.14 - 175.62	0.58	20	0.58	-
5-1907125-4	53.460 - 54.540	175.39 - 178.93	0.58	20	0.58	-
5-1907125-5	54.450 - 55.550	178.64 - 182.25	0.58	20	0.58	-
5-1907125-6	55.440 - 56.560	181.88 - 185.56	0.58	20	0.58	-
5-1907125-7	56.430 - 57.570	185.13 - 188.87	0.59	20	0.59	-
5-1907125-8	57.420 - 58.580	188.38 - 192.19	0.59	20	0.59	-
5-1907125-9	58.410 - 59.590	191.63 - 195.50	0.59	20	0.59	-
6-1907125-0	59.400 - 60.600	194.88 - 198.81	0.59	20	0.59	-
6-1907125-1	60.390 - 61.610	198.12 - 202.13	0.59	20	0.59	-
6-1907125-2	61.380 - 62.620	201.37 - 205.44	0.59	20	0.59	-
6-1907125-3	62.370 - 63.630	204.62 - 208.75	0.59	20	0.59	-
6-1907125-4	63.360 - 64.640	207.87 - 212.07	0.6	20	0.6	-
6-1907125-5	64.350 - 65.650	211.12 - 215.38	0.6	20	0.6	-
6-1907125-6	65.340 - 66.660	214.37 - 218.70	0.6	20	0.6	-
6-1907125-7	66.330 - 67.670	217.61 - 222.01	0.6	20	0.6	-
6-1907125-8	67.320 - 68.680	220.86 - 225.32	0.6	20	0.6	-
6-1907125-9	68.310 - 69.690	224.11 - 228.64	0.6	20	0.6	-
7-1907125-0	69.300 - 70.700	227.36 - 231.95	0.61	20	0.61	-
7-1907125-1	70.290 - 71.710	230.61 - 235.26	0.61	20	0.61	-
7-1907125-2	71.280 - 72.720	233.85 - 238.58	0.61	20	0.61	-
7-1907125-3	72.270 - 73.730	237.10 - 241.89	0.61	20	0.61	-
7-1907125-4	73.260 - 74.740	240.35 - 245.20	0.61	20	0.61	-
7-1907125-5	74.250 - 75.750	243.60 - 248.52	0.61	20	0.61	-
7-1907125-6	75.240 - 76.760	246.85 - 251.83	0.61	20	0.61	-
7-1907125-7	76.230 - 77.770	250.09 - 255.15	0.62	20	0.62	-
7-1907125-8	77.220 - 78.780	253.34 - 258.46	0.62	20	0.62	-
7-1907125-9	78.210 - 79.790	256.59 - 261.77	0.62	20	0.62	-
8-1907125-0	79.200 - 80.800	259.84 - 265.09	0.62	20	0.62	-

THIS DRAWING IS A CONTROLLED DOCUMENT. BFC#

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS TO BE KEPT CONFIDENTIAL AND NOT DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

LOC  
CE  
DIST  
16

A	Rev Per EC#	RELEASE	2/15/2006	-	DF		
P	LTR	REVISION RECORD	DATE	DIN	APVD		

Customer Print

DIAMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	
9 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±

DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	-
CHK	Dave Fennell	Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Dave Fennell				
NAME	FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1907125
SHEET	3 of 4	REV	A		

A  
B  
C  
D

Restricted to: General Release

**Label 1** Per specification 107-1645-1



This label is used on all lengths on this drawing.

**Label 2** Per specification 107-1645-1



This label is used on all lengths on this drawing.

THIS DRAWING IS A CONTROLLED DOCUMENT.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC  
CE  
DIST  
16

A	Rev Per	EC#	RELEASE	2/15/2006	-	DF	
P	LTR		REVISION RECORD	DATE	DIN	APVD	

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC	± .
1 PLC	± .
2 PLC	± .
3 PLC	± .
4 PLC	± .

Customer Print

DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	-
CHK	Dave Fennell	Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Dave Fennell				
NAME	FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1907125
SHEET	4 of 4	REV	A		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1907394-7](#)