



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICITY

ALL RIGHTS RESERVED

LOC —	DIST —	REVISIONS							
		P	LTR	DESCRIPTION		DATE	DWN	APVD	
		A		PRODUCTION RELEASE PER ECO-13-014747			9-18-13	CT	RL



1 CONNECTOR BODY AND COUPLING SLEEVE MATERIAL:  
6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404  
LOCKING RING MATERIAL: BERYLLIUM COPPER, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404  
INSULATOR MATERIAL: LIQUID CRYSTAL POLYMER (LCP) PER ASTM D5138  
O-RING MATERIAL: FLUOROSILICONE PER SAE-AMS-R-25988

2 O-RING MATERIAL: FLUOROSILICONE PER SAE-AMS-R-25988  
TERMINATED WITH MADISON CABLE 30 AWG 10G TURBO TWIN PAIR

 CABLE LENGTH IS AS INDICATED IN THE CORRESPONDING NANONICS PART NUMBER

5 LUBRICATE O-RING WITH PARKER SUPER-O-LUBE PRIOR TO INSTALLATION

6 REFERENCE TE PRODUCT SPECIFICATION 108-32048 FOR PRODUCT DETAILS AND PERFORMANCE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M STORRY CHK M STORRY APVD M STORRY	31 JUL 2012 31 JUL 12 31 JUL 12	 TE Connectivity		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME PLUG ASSEMBLY, CIRCULAR, QUICK DISCONNECT W/ FLANGED COUPLING SLEEVE, METAL, 8 POSITION, 10GbE, CeeLok FAS-T Nano Circular				
	0 PLC ± - 1 PLC ± - 2 PLC ± .010 3 PLC ± .005 4 PLC ± - ANGLES ± 1°	PRODUCT SPEC — APPLICATION SPEC —				
MATERIAL SEE NOTES	FINISH SEE NOTES	WEIGHT —	SIZE A2	CAGE CODE 0JPN9	DRAWING NO C-1925254	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 6:1	SHEET 1 OF 1	REV A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[FCM008PC1TT036](#)