




1470-19 (3/11)



4

3




2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
ES	—		—	SEE SHEET 1	—	—	—



- (APPLIED TO SHEET 4)
1. THE DIRECTION OF EACH CONNECTOR ON A EMBOSS IS REFERRED TO THIS DRAWING.
 2. GENERAL TOLERANCE: ± 0.5 , $\pm 3^\circ$



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity DDR3 SODIMM SOCKET 0.6mm PITCH 204POS 9.2mm HEIGHT STANDARD TYPE			
		CHK				
		APVD				
		PRODUCT SPEC				
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME			
		0 PLC ± 0.5	SIZE			
		1 PLC ± 0.5	CAGE CODE			
		2 PLC ± 0.5	DRAWING NO			
		3 PLC ± 0.5	RESTRICTED TO			
		4 PLC ± 0.5	A300779C-1932209			
		ANGLES $\pm 3^\circ$	SCALE			
		FINISH	1:2			
MATERIAL			SHEET			
			4 OF 4			
			REV			
			C			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1932209-2](#)