

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A5	REVISED PER ECO-16-018632	05APR2017	SK	PO

SPECIFICATIONS:

MATERIALS:
CASE, PPS, UL94 V-0, BROWN
ACTUATOR, NYLON, UL94V-0, SEE P/N TABLE FOR FINISH
COVER, STEEL, TIN FINISH
TERMINAL/FIXED CONTACT, COPPER ALLOY-SILVER FINISH
MOVING CONTACT, STAINLESS STEEL-SILVER FINISH

ELECTRICAL:
MAX CONTACT RATING, 50MILLIAMP@24V DC
MIN CONTACT RATING, 1MICROAMP@1V DC
CONTACT RESISTANCE, 100 MILLIOHMS MAX
INSULATION RESISTANCE, 100 MEGOHM MIN.
DIELECTRIC STRENGTH, 500 V AC FOR 1 MINUTE
LIFE EXPECTANCY, 1,000,000 CYCLES


MECHANICAL:
ACTUATION FORCE, SEE P/N TABLE
ACTUATION TRAVEL, 0.25 +0.20/-0.10
LIFE EXPECTANCY, 1,000,000,
(2 CYCLES PER SECOND AND 150% ACTUATION FORCE)

ENVIRONMENTAL:
OPERATING TEMPERATURE, -40 TO +105° C
STORAGE TEMPERATURE, -40 TO +105° C
SOLDERABILITY, EIA-RS-186-9E, OR MIL-STD-202F
RESISTANCE TO SOLDER HEAT, 260° C FOR 10SEC-PER 109-201, COND B
1. NO CHANGE IN INITIAL ELECTRICAL AND MECHANICAL CHARACTERISTICS

NOTES:

- 1 TAPE AND REEL PACKAGING PER EIA 481.
- 2 ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)

()-INDICATES MOMENTARY POSITION		
CIRCUIT CHARACTERISTICS		
CONTACT POSITION	CIRCUIT DIAGRAM	
OFF	(ON) 1 - 3 2 - 4	



FSM2JSMA AS SHOWN

DIM B (7.01[.276]) AND LONGER MODELS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 07NOV2007	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK M.SARVER 07NOV07				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.30[.012] 3 PLC ± - 4 PLC ± - ANGLES ± 1°		MICRO MINIATURE PUSHBUTTON SWITCH FSM JSM			
MATERIAL		APVD M.SARVER 07NOV07	PRODUCT SPEC		SIZE A2	RESTRICTED TO
FINISH		APPLICATION SPEC	WEIGHT 0		CAGE CODE 00779	REV A5
		CUSTOMER DRAWING	SCALE 8:1		SHEET 1 of 2	

4		3		2		1					
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		2-1437565-7 , 2-1437565-7		REVISIONS					
© COPYRIGHT 2-1437565-7		ALL RIGHTS RESERVED.				P	LTR	DESCRIPTION	DATE	DWN	APVD
							-	SEE SHEET 1	-	-	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1977223-1](#)