

APPLICATOR PARTS LIST

TYPE

SIDEWISE Amp-LOK

AMP INCORPORATED
HARRISBURG, PENNA.

NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA	TERMINALS
1	WIRE CRIMPER 1-453936-3	1	453936-3	42	Shear Plate Left	1	811855-1	TO APPLY TERMINAL	42641-
2	INS. CRIMPER & Stab. (.160)	1	465604-3	43	Right Shear Guide Block	1	387219		.0126 Stk.
3	ANVIL	1	810765-1	44	Floating Shear	1	465106	WIRE SIZE	350 Feed
4	ANVIL SPACER	1	810017-0	45	Retaining Plate-Front	1	811714-3	CRIMP HEIGHT	
5	SHEAR BLADE			46	Retaining Plate- Rear	1	810822-1	WIRE SIZE	
6	REAR SHEAR PLATE			47	Spring-Shear Return	1	371322	CRIMP HEIGHT	
7	SHEAR BLADE SPACER			48	Shear Depressor 453302	1	387255	WIRE SIZE	
8	FRONT SHEAR PLATE			49	Key - Shear Retainer	1	386358	CRIMP HEIGHT	
9	REAR ANVIL SPACER PLT.			50	Adj. Strip Guide Plate	1	692035-1	WIRE SIZE	
10	FRONT ANVIL SPACER PLT.			51	Rear Adj. Block	1	387252	CRIMP HEIGHT	
11	TOOL SPACER			52	Wire Stop Holder Spacer	1	387280	WIRE SIZE	
12	CRIMP SPACER	1	372177	53	Rear Hold Down Holder	1	810771-1	CRIMP SIZE	
13	STRIP GUIDE Plate-Feed	1	387218	54	Rear Hold Down	1	694947-1	CRIMP TYPE	
14	REAR STRIP GUIDE	1	387250	55	Hold Down Pin	1	810768-1	CRIMP FEED	
15	RAM	1	471912	56	Plunger Tip	1	810767-1	WIRE	
16	TOOL HOLDER			57	Spring - Hold Down	1	810773-1	INSUL.	
17	ADJ. CRIMP MOUNT Assy.	1	465392-6	58	Anvil Pack-Up Block	1	810769-1	SLEEVED	
18	ADJ. BLOCK			59	Front Strip Hold	1	810799-1	WIRE RANGE	
19	APPLICATOR MOUNT ASSY.			60	Guard Mount	1	811906-1	EXPLODED VIEW	
20	BASE PLATE	1	473171	61				REMARKS:	
21	BASE BLOCK	1	465002-3	62					
22	STRIP GUIDE PLATE 692034-1	1	473171	63	Wire Stop Guide	1	811787-1		
23	ANVIL HOLDER			64	Tension Adj. Plate	1	374999		
24	AUX. ANVIL HOLDER			65					
25	STRIPPER			66	Punch Holder	1	810498-1		
26	STRIPPER MOUNT 386362	1	386362	67	Button Hd. CapScr. 10-32x1/2	1	2-21002-		
27	Wire Stop	1	386361-1	68	Hex Nut 10-32	1	21018-7		
28	STRIPPER MOUNT BRACKET	1	386375	69	2 Pk. 21018-7 Supply Classy	1	465050-2		
29	STRIPPER BUSHING	1	389019-1	70					
30	STOCK DRAG	1	387230	71					
31	STOCK DRAG HANDLE			72	MECH FEED ASSY	1	692140-2		
32	STOCK DRAG STUD			REV.	REVISION RECORD	DATE	BY	ECN	
33	STOCK DRAG SPRING	1	373169	1	REV FROM 54	11-24-77	IM	1-7135	
34	STOCK DRAG ADJ. Knob	1	21022-3	D	ITEM 22 WAS 50 WAS 273470	3-9-70	RS	1-74-09	
35	FEED FINGER HOLDER	1	386912	D	OBS TYPED 60204	3-23-70	RS	1-74-09	
36	FEED FINGER	1	810111	E	REV 72 & C.H	3-3-71	RS	1-8138	
37	FEED FINGER TIP	1	387251	F	REV PER ECN	7-26-71	RS	1-8409	
38	FEED FINGER SPACER			G	ITEM 46 WAS 387265-1, 67472	1-71	RS	1-8552	
39	BASE CASTING	1	570238	H	REV PER ECN	3-29-73	RS	1-9610	
40	GUARD 457665-2	1	457665-2	HI	INACTIVE ENG	7-17-77	RS	1-9710	
41	Bracket	1	811901-1						

— INACTIVE —
FOR REPLACEMENT ONLY

■ DENOTES WEARING PARTS
RECOMMEND PURCHASE REPLACEMENT

THIS APPLICATOR IS TO BE USED ON

AMP-O-ELECTRIC 1-471273-3

AMP-O-MATIC MECH FEED

Alignment Gage R-678498

SERIAL NO. DATE SHIPPED

CUSTOMER NAME AND ADDRESS

DESIGNED

CHK'D

APP'D

SHEET

1 OF 1

APPLICATOR NUMBER

RF

1-672454-2

B/R1710

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-672454-2](#)