




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₀	RELEASED	03/21/95	<i>AD</i>

COPY IN PUERTO RICO
DESIGN CONTROL REQUIRED

HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197 ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
RETAINING RING	BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, CONDITION H	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		
FRAC. ± 1/64	DEC. ±.005	ANGLES ± 1°
DRAWN BY <i>J. Davis</i> DATE 03/21/95 CHECKED BY APPD BY		AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599
These drawings and speci- fications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale o f item(s) without written permission.		TITLE TYPE N PLUG TO SMA JACK ADAPTER
USE ASSY PROCEDURE N/A NO. A.P. _____		SIZE B CODE IDENT NO. 26805 1250-1250-00 REV 01 ₀
SCALE 5=1		SHEET 1 OF 1

NOTES:

- CAPTURED CENTER CONTACT
- VSWR: DC-12.4GHz :1.06+.005fGHz MAX
12.4-18.0GHz : 0.83+.023fGHz MAX

.XXX = in
XX.X = mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1250-1250-00](#)