


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
010	RELEASED	3/22/95	M.M.

DESIGN CONTROL REQUIRED

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
COMPONENT	MATERIAL	FINISH

- NOTES:
- 1. DESIGNED FOR USE WITH .085 DIA SEMI-RIGID CABLE
 - 2. CAPTURED CENTER CONTACT

CABLE ENTRY DIAMETER MINIMUM		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON		DRAWN BY <i>M.M.</i> DATE 3/22/95		 AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	
HOUSING	.089	FRACTIONAL	DECIMAL	ANGLES	CHECKED BY		
CONTACT	.021	± 1/64	± .005	± 1°	APPROVED BY		
		These drawings and specifications are the property of M/A-COM Interconnect Division and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		USE ASS'Y PROCEDURE		TITLE	
				408-04833 (20-010)		OSM STRAIGHT CABLE JACK DIRECT SOLDER ATTACHMENT	
				NO. A.P.		SIZE B	CODE IDENT NO. 26805
						SCALE 5:1	1250-1989-00
						REV 010	
						SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1250 1989 00](#)