




DESIGNED FOR USE WITH RG-188/U		REVISIONS			
		REV	DESCRIPTION	DATE	APPROVED
CABLE ENTRY DIAMETER MINIMUM		01 <sub>2</sub>	REVISED	9/13/2017 	
CONTACT	.021				
DIELECTRIC	.023				
SLEEVE	.066				
FERRULE	.125				

HOUSING CLAMP NUT SLEEVE	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
O-RING	SILICONE RUBBER PER ZZ-R-765	N/A
SHRINK TUBING	HEAT SHRINKABLE POLYOLEFIN COMPOUND MIL-I-23053/4	N/A
FERRULE	COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM	GOLD PLATE PER MIL-G-45204
COMPONENT	MATERIAL	FINISH
<div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES</div> <div><div><div>FRAC. ± 1/64</div><div>DEC. ±.005</div><div>ANGLES ± 1°</div></div><div><div>DRAWN BY FMC</div><div>CHECKED BY KWW</div><div>APPD BY RMF</div></div><div><div>DATE 9/15/77</div><div>9/21/77</div><div>9/21/77</div></div><div><div></div><div><div>AMP Incorporated</div><div>140 Fourth Avenue</div><div>Waltham, MA 02451-7599</div></div></div></div>		
These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE	TITLE
	408-04808 (20-057)	"OSM" STRAIGHT CABLE JACK CRIMP-CLAMP ATTACHMENT
	NO. A.P.	<div><div>SIZE B</div><div>CODE IDENT NO. 26805</div><div>2032-5003-02</div><div>REV 01<sub>2</sub></div></div>
		SCALE 5:1

NOTES:  
1. CAPTURED CENTER CONTACT

.XXX = in  
XX.X = mm (REF)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2032-5003-02](#)