



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₁	REVISED	11/14/86	



HOUSING INNER SLEEVE	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35			
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A			
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204			
COMPONENT	MATERIAL	FINISH			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY DAC 11/10/88	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599			
FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	CHECKED BY DAC 11/23/88				
	APPROVED BY AW 11/28/88				
These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE	TITLE OS-50 JACK TO OS 2.9 JACK			
	NO. A.P. N/A	SIZE B	CODE IDENT NO. 26805	8580-2361-02	REV 01
		SCALE 6:1			SHEET 1 OF 1

NOTES:
1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm (REF)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8580-2361-02](#)