






56P HYBRIDE PLUG KEY CODE.			
P/N	"A"	COLOR	MATERIAL
0-1743130-2	48	BLACK	PBT
1-1743130-3	40	GRAY	PBT



NOTE.
1. GENERAL TOLERANCE IS $\pm 0.3, \pm 3^\circ$
2. CONDITION OF DELIVERY : DBL PLATE PRE-ASSEMBLED POSITION
3. APPLIED RECEPTACLE CONTACT P/N:

	PART No.	WIRE SIZE(mm ²)
MCP-E	0-1743162-1	0.3 0.85mm ²
	0-1743163-1	1.25 2.0mm ²
MCP 6.3	0-1241400-1	0.2 0.5mm ²
	0-1241402-1	0.5 1.0mm ²
	0-1241404-1	1.0 2.5mm ²
	0-1241406-1	2.5 4.0mm ²
	0-1241408-1	4.0 6.0mm ²

4. APPLICABLE COVER PART No.: 1743133, 1743588, 1743589
5. MATING BOLT Torque spec 0.8-1.0 Kgf.m

				1-1743130-3	0-1743130-2	ASSY P/N
3	M6 NUT	-	SUM24L	1	1	
2	DBL	NATURAL	PBT	2	2	
1	PLUG	GRAY	PBT	1	•	
		BLACK	PBT	•	1	
	NAME	COLOR	MATERIAL	Q'TY		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

3rd ANGLE PROJECTION

MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

SEE NOTE

FINISH

DWN
DH PARK
CHK
YJ YOUN
APVD
JK SONG
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
-

NAME

-

SIZE
A3

CAGE CODE
00779

DRAWING NO
1743130

RESTRICTED TO

AMP KOREA.
kyungsan, korea

HYBRID 56P PLUG ASS'Y
(NUT TYPE)

CUSTOMER DRAWING

SCALE 1/1

SHEET 1 OF 1

REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1743130-3](#)