

8			7		
THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION		
20			20		
(C) COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.					
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION
1852201-1	C	122500-1	LEADMAKER	POST FEED	CUTS CARRIER
1852201-2	C	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER
1852201-3	C	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER
1852201-6	C	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER
7-1852201-7	C	-	-	-	SPARE PARTS


1 RECOMMENDED SPARE PARTS

2 GREASE LIGHTLY


3 GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE

4 THIS IS NOT A PACKARD RECOMMENDED WIRE SIZE.

5. THIS TERMINAL REQUIRES LUBRICATION.



TERMINAL NAME: TERMINAL, MALE, .56 SERIES					
TYCO PN	MANUF PN	PACKARD TERM - AMP CRIMP SPECS			
1572958	2971859				
-	-	PAD LTR	CRIMP HEIGHT		WIRE SIZE
-	-	A	.119±.002[3.02±0.05mm]		12 AWG
-	-	B	.116±.002[2.94±0.05mm]		14 & 16 AWG
-	-	C	.112±.002[2.84±0.05mm]		(2) 16 AWG
-	-	D	.106±.002[2.69±0.05mm]		(2) 18 AWG
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	.177 [4.50mm]	F	(2)18 - 12 AWG
-	-	INSUL	.210 [5.33mm]	F	Ø3.05mm-2.48mm
WIRE STRIP LENGTH .171 - .186		TERM APPL SPEC NONE	FEED .625	APPL INSTRUCTIONS 408-8040	SET UP GAGE 458637-1



-	2	2	2	2	-	8-354778-1	PIN, WIRE DISC, .2900	129
-	2	2	2	2	-	6-354778-9	PIN, WIRE DISC, .2840	128
-	2	2	2	2	-	6-354778-1	PIN, WIRE DISC, .2800	127
-	2	2	2	2	-	5-354778-4	PIN, WIRE DISC, .2765	126
-	3	3	3	3	-	2-22733-8	SCR, BHSC, SELF-LOCKING, 1/4-20 X .625	125
-	1	1	1	1	-	690432-3	ADJUSTMENT SCREW	124
-77	-6	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO

LOC	DIST	REVISONS							
A	66	P	LTR	DESCRIPTION		DATE	DWN	APVD	
		B		ECR 06-018444		31JUL2006	MEH	GB	
		C		ECR 06-021158		01SEP2006	MEH	GB	
-	1	1	1	1	-	3-21028-8	PIN, SLOTTED SPRING .094 X .625	121	
-	1	1	1	1	-	461062-1	ASSEMBLY, FEED FINGER	117	
-	-	-	REF	-	-	455749-1	GUARD WINDOW	116	
-	-	REF	-	-	-	679532-1	INSERT, GUARD	115	
-	4	4	4	4	-	21024-2	WASHER, SPRG LOCK, REG NO 4	114	
-	-	-	1	-	-	1-465184-0	LUBRICATOR ASSY	113	
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112	
-	1	1	1	1	-	3-21001-5	SCR, SKT HD CAP 3/8-16 X 1.000	111	
-	-	-	-	-	-	459610-1	MOUNT, FEED BRACKET	110	
-	1	1	1	1	-	21024-8	WASHER, SPRG LOCK, REG 3/8	109	
-	1	1	1	1	-	692655-5	AIR FEED VALVE ASSEMBLY	108	
-	1	1	1	1	-	692655-7	AIR FEED VALVE ASSEMBLY	105	
-	1	1	1	1	-	461065-1	ASSEMBLY, AIR FEED	104	
-	2	2	2	2	-	3-21000-9	SCR, SKT HD CAP 10-32 X 1.000	103	
-	1	1	1	1	-	22353-8	SCR, SHLD, SLOT HD, 3/16 DIA	100	
-	2	2	2	2	-	5-21006-6	SCR, SET, CUP POINT 10-32 X .750	99	
-	4	4	4	4	-	2-21002-9	SCR, BTN SKT HD CAP 10-32 X .750	97	
-	1	1	1	1	-	2-21002-7	SCR, BTN SKT HD CAP 10-32 X .500	95	
-	-	-	1	-	-	2-21002-6	SCR, BTN SKT HD CAP 10-32 X .375	93	
-	2	2	2	2	-	1-21000-3	SCR, SKT HD CAP 4-40 X .250	91	
-	2	2	2	2	-	2-21002-0	SCR, BTN SKT HD CAP 8-32 X .250	89	
-	1	1	1	1	-	2-22603-0	SCREW, MACH, HEX HD, 8-32 x .312	86	
-	2	2	2	2	-	1-21000-5	SCR, SKT HD CAP 4-40 X .500	85	
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72	
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71	
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67	
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66	
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64	
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63	
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62	
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60	
-	1	1	1	1	-	454220-1	CAP, RAM	59	
-	1	1	1	1	-	454485-1	HOUSING, SIDE FEED	58	
-	1	1	1	1	-	1633145-1	PLATE, BASE	57	
-	1	1	1	1	-	3-694433-9	FEED PAWL	56	
-	2	2	2	2	-	3-21000-1	SCR, SKT HD CAP 8-32 X 1.000	53	
-	1	1	1	1	-	1633487-1	HOLDER, SLUG BLADE	50	
-	1	1	1	1	-	690191-1	PLUG, NYLON	45	
-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44	
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43	
-	1	1	1	1	-	690124-7	WASHER, RAM (.090)	42	
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41	
-	1	1	1	1	-	23241-6	BALL, STEEL	40	
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39	
-	1	1	1	1	-	690142-1	DISC, INSULATION	38	
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37	
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36	
-	1	1	1	1	-	690212-1	POST, RAM	35	
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	33	
-	3	3	3	3	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32	
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31	
-	1	1	1	1	-	455689-1	BLOCK, STRIP GUIDE ADJUST	30	
-	1	1	1	1	-	2-844048-4	PLATE, REAR STRIP GUIDE	29	
-	2	2	2	2	-	22282-1	SPRING, COMPRESSION	27	
-	1	1	1	1	-	240793-1	LEVER, DRAG RELEASE	26	
-	1	1	1	1	-	240792-1	DRAG, TERMINAL	25	
-	1	1	1	1	-	1633497-1	REAR STRIP GUIDE	24	
-	1	1	1	1	-	2-189124-1	GUIDE, FRONT STRIP	23	
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21	
-	2	2	2	2	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20	
-	1	1	1	1	-	1-456468-1	STRIPPER, SPECIAL	19	
-	2	2	2	2	-	1-21000-5	SCR, SKT HD CAP 4-40 X .500	16	
-	1	1	1	1	-	1633489-1	BLADE, SLUG	15	
-	1	1	1	1	-	1633490-1	PLATE, SHEAR	13	
-	-	1	1	1	-	1725849-2	BLADE, SLUG	10	
-	1	1	1	1	-	1633488-1	SHEAR, LOWER	9	
1	1	1	1	1	-	5-1633116-6	ANVIL, COMBINATION	8	
-	1	1	1	1	-	1-240641-8	SPACER	7	
-	1	1	1	1	-	5-240641-9	SPACER	6	
-	1	1	1	1	-	2-238009-5	BLOCK, FL CRIMPER SPACER	4	
1	1	1	1	1	-	9-1424909-1	CRIMPER, INSULATION F	3	
-	1	1	1	1	-	1-455888-1	SPACER, CRIMPER	2	
1	1	1	1	1	-	5-1633305-1	CRIMPER, WIRE PREMIUM	1	
-77	-6	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO	

THIS IS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE KEPT IN CONFIDENCE AND NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION, NO PART OF THIS DRAWING SHOULD BE COPIED OR REPRODUCED FOR ANY PURPOSE.		DWN	13MAR2006	tyco Tyco Electronics	
CHK		14MAR2006	R. KNEPPER		Harrisburg, PA 17105-3608
APVD		14MAR2006	T. ERLIN		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
INCHES		9 PLC ±.01		PRODUCT SPEC	
		1 PLC ±.01		APPLICATION SPEC	
		3 PLC ±.001		SIZE	
		4 PLC ±.0001		CAGE CODE	
MATERIAL		FINISH		DRAWING NO	
				RESTRICTED TO	
				WEIGHT	
				A1 00779	
				CUSTOMER DRAWING	
				SCALE 3:5	
				SHEET 1 OF 1	
				REV C	

CUSTOMER VIEWABLE ASSEMBLY

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852201-1](#)