



- 1 POLYESTER, PBT, 15% GLASS FIBER REINFORCED, NATURAL, PER MIL-M-24519.
- 2 ZINC PER QQ-Z-363.
- 3 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 4 PHOSPHOR BRONZE PER QQ-B-750.
- 5 BRASS PER QQ-B-626.
- 6 BRASS PER ASTM-B-453.
- 7 NICKEL PL PER QQ-N-290, 3.81µm [0.000150] MINIMUM THICK
- 8 GOLD PL PER MIL-G-45204, 0.76µm [0.000030] MINIMUM THICK
- 9 TIN-LEAD PL PER ASTM-B-545 & MIL-P-81728, 3.81µm [0.000150] MINIMUM THICK



RECOMMENDED
PANEL CUTOUT

PCB CONFIGURATION

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PL DEC = ±.001 3 PL DEC = ±.002 ANGLES = ±.001		DR 10/22/90 R.E. ROTH	CHK 3-8-91 A. JASANY	APPO 3-8-91 1. JASANY	APPO 3-8-91 J. L. JASANY	PRODUCT SPEC 108-12078	APPLICATION SPEC -	WEIGHT -
MATERIAL 1 2 3 4 5 6 7 8 9		NAME JACK, VERTICAL, PCB, SERIES TWIN BNC		SIZE D		CAGE CODE 00779	DRAWING NO 228697	SHEET 1 OF 1

228697-2
PART NO

AMP AMP Incorporated
Harrisburg, PA 17105-3608

JACK, VERTICAL, PCB,
SERIES TWIN BNC

SIZE
D

SCALE
5:1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[228697-2](#)