

SHOW PART NR & VENDOR IN AREA MARKED X
(INCLUDE DASH NR & REVISION LTR)

1-6'89 REIASED

USED ON


DOWEL PIN, DIN 9861

MAT: STEEL



Joveka bv

OPRIE VRIJSTRAATKADE 9
POSTBUS 4025
1009 AA AMSTERDAM.
TEL. 320 - 682121
TELEX: 11420



PART NO	d	L	ORDER NUMBER*
431672-1	3	14	3h6 X 14 DIN9861-ST
431672-2	3	28	3h6 X 28 DIN9861-ST
431672-3	4	20	4h6 X 20 DIN9861-ST
431672-4	4	30	4h6 X 30 DIN9861-ST
431672-5	4	36	4h6 X 36 DIN9861-ST
431672-6	4	70	4h6 X 70 DIN9861-ST
431672-7	5	20	5h6 X 20 DIN9861-ST
431672-8	6	36	6h6 X 36 DIN9861-ST
431672-9	6	60	6h6 X 60 DIN9861-ST
1-431672-0	8	36	8h6 X 36 DIN9861-ST
1-431672-1	8	60	8h6 X 60 DIN9861-ST
1-431672-2	12	70	12h6 X 70 DIN9861-ST
1-431672-3	3	10	3h6 X 10 DIN9861-ST
1-431672-4	6	14	6h6 X 14 DIN9861-ST

* ORDER NUMBER: d h6 X L DIN9861-ST

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP-HOLLAND B.V.

DISTR

QTY REQD PER ASSY			DWG SIZE	PART NO	DESCRIPTION	ITEM NO
← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)						
PARTS LIST			MATERIAL <u>COMMERCIAL</u> (W. ST. NR.)			
			HEAT TREAT <u>—</u>		FINISH <u>—</u>	
			TOLERANCES UNLESS OTHERWISE SPECIFIED. REMOVE BURRS. ANGLES ± 0°30'			
			<div style="display: flex; justify-content: space-between;"> <div>INCHES $\frac{.00}{.0000} \pm .00$ $\frac{.0000}{.0000} \pm .0000$ </div> <div>MILL METRES ± 0.5 ± 0.2 ± 0.02 ± 0.005 </div> </div>			
			DR. <u>F.H. 10-4-'89</u>		AMP HOLLAND B.V.	
			CHK. <u>A.Z. 6-6-'89</u>		's-Hertogenbosch, The Netherlands	
			First used		NAME <u>DOWEL PIN, DIN9861</u>	
LTR	ECN	DATE	SCALE	SHEET 1 OF 2	LOC	SIZE NO <u>431672</u>

USED ON

04




437672

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP-HOLLAND B.V.

[illegible]

* ORDER NUMBER : dh6 x L DIN 9861-ST

DISTR

			DWG SIZE	PART NO	DESCRIPTION		ITEM NO
			 REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)				
QTY REQD PER ASSY			PARTS LIST				
			MATERIAL COMMERCIAL (W. ST. NR. <i>H</i>)		HEAT TREAT <i>H</i>		FINISH <i>H</i>
			DIMENSIONS IN TOLERANCES UNLESS OTHERWISE SPECIFIED. REMOVE BURRS. ANGLES $\pm 0^{\circ}30'$				
			<div style="display: flex; justify-content: space-between;"> <div style="text-align: center;"> INCHES $.00 \pm .02$ $.000 \pm .005$ $.0000 \pm .0005$ </div> <div style="text-align: center;"> MILLIMETRES $\pm 0,5$ $\pm 0,2$ $\pm 0,02$ $\pm 0,005$ </div> </div>				
			DR. <i>J. v. RIJN 28-9-'89</i>		<div style="display: flex; align-items: center;">  <div> AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands </div> </div>		
			CHK.				
			First used <i>H</i>		NAME <i>DOWEL PIN, DIN 9861</i>		
							
LTR	ECN	DATE	SCALE	SHEET	LOC	SIZE	NO <i>174170</i>
			REV				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-431672-3](#)