


SOCKET (7)
MAT'L: COPPER ALLOY APPROVED
PER MIL-C-39029
FINISH: GOLD PER MIL-G-45204

- 1 TEFLON INSULATED WIRE PER MIL-W-16878/5
2 AMP INFORMATION MARKED PER MIL-STD-130.
3 NUMBERS SHOWN FOR REFERENCE ONLY.



SECTION T-T

7	BLUE	#20 AWG	SILICONE	.161
6	RED	#20 AWG	SILICONE	.161
5	-	-	-	-
4	BLACK	#22 AWG	TEFLON 1	.050
3	BROWN	#22 AWG	TEFLON 1	.050
2	YELLOW	#22 AWG	TEFLON 1	.050
1	GREEN	#22 AWG	TEFLON 1	.050
PIN	COLOR	AWG	INSULATION	O.D.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES [mm]
TOLERANCES ON:
2 PLC DEC ± .01 [0.3]
3 PLC DEC ± .005 [0.13]
ANGLES ± 0°30'

MATERIAL

SEE CALLOUTS

FINISH

SEE CALLOUTS

DR 5-20-92
C.C. THOMASCHK 5-27-92
D.EABYAPPD 5-27-92
D.EABYAPPD 5-27-92
C.C. THOMAS

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

AMPAMP Incorporated
Harrisburg, PA 17105-3608

NAME

TUBE BASE, LGH, 7 POSN.
EIA E7-91

SIZE

C

CAGE CODE

00779

DRAWING NO

C=448335

SCALE

2:1

SHEET

1 OF 1

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[448335-1](#)