


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		, 19 .	
© COPYRIGHT 19		BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.			

LOC	DIST	P	F	REVISIONS				
AF	50			ZONE	LTR	DESCRIPTION	DATE	APPD
					C	REV PER 0041-94	6/15/94	JR/SG



- 1 MATES WITH A SPECIAL .020±.001X.110 TAB FOR LANDIS AND GYR.
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .120 MAX DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

HOUSING: NYLON, COLOR-RED TRANSLUCENT		2-521010-2	
RECEPTACLE: #3 HARD BRASS			
TIN PL .000080 MIN THK			
MATERIAL & FINISH			PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± -	DR 12/4/92 JR RUTH	<b>AMP</b> AMP INCORPORATED Harrisburg, Pa. 17105	
	CHK 12/4/92 MS FEHER		
	APPD 12/4/92 D BRATINA	NAME RECEPTACLE ASSY, ULTRA-FAST, .110 SERIES, 22-18 AWG	
	APPD 12/4/92 V KARA.		
MATERIAL SEE TABLE	PRODUCT SPEC 108-2043	SIZE <b>B</b>	FSCM NO 00779
FINISH SEE TABLE	APPLICATION SPEC 114-2123	DRAWING NO 521010	
WEIGHT -		SCALE 5:1	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-521010-2](#)