



LOC		DIST		P		ZONE		LTR		REVISIONS		DATE		APPD	
AF	50									J	REVISED PER 0710-0491-95	02NOV95		R6/NN	

- 1 0.00508 [.000200] MIN TIN IN FUNCTIONAL PLATE AREA, 0.00254 [.000100] MIN TIN ON REMAINDER, OVER 0.00254 [.000100] MIN COPPER UNDERPLATE.
- 2 PRODUCT COMPLIES WITH AMP SOLDERABILITY SPEC 109-11-5 WHEN PLATED AND 109-11-1 AFTER TWO YEARS OF SHELF LIFE.
- 3 DATUMS AND BASIC DIMENSIONS TO BE DETERMINED BY CUSTOMER.
- 4 FITS A 0.508±0.025 [.020±.001] THICK TAB. 12 PLACES
- 5 CUSTOMER SIGNIFICANT CHARACTERISTIC.

1		H04 PRE-MILLED BRASS		12		TAB RECEPTACLE		2		521018-1	
BLACK		LIQUID CRYSTAL POLYMER		1		HEADER HOUSING		1			
FINISH		MATERIAL		QUANTITY		DESCRIPTION		ITEM NO		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 [3] PLC DEC ± 0.25 [.010] 3 [3] PLC DEC ± 0.10 [.004] ANGLES ± -				DR 1/18/93 MICHAEL S. FEHER CHK 1/20/93 JEFF R. RUTH APPD 1/20/93 NELSON E. NEFF APPD 1/20/93 TERRY L. SHUTTER		AMP Incorporated Harrisburg, PA 17105-3608					
MATERIAL SEE TABLE				PRODUCT SPEC -		NAME ASSEMBLY, HEADER, RECEPTACLE, TAB, 2.79 [.110], P.C. BOARD, 12 POSITION, MAG-MATE™					
FINISH SEE TABLE				APPLICATION SPEC -		SIZE D		CAGE CODE 00779		DRAWING NO C-521018	
WEIGHT -				SCALE 4:1				SHEET 1 OF 1			

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[521018-1](#)