

SHIFTED
7-5ERR

NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.
1	WIRE CRIMPER .125 FLAT	1	455713-2	42	SCREW, SOC. HD. CAP	2	811651-5
2	INS. CRIMPER			43	WASHER, LOCK	2	21057-4
3	ANVIL .125 FLAT	1	455714-2	44	STRIP HOLD DOWN	1	810640-2
4	ANVIL SPACER			45			
5	SHEAR BLADE	1	693012-1	46			
6	REAR SHEAR PLATE	1	465891-1	47			
7	SHEAR BLADE SPACER			48			
8	FRONT SHEAR PLATE			49			
9	REAR ANVIL SPACER PLT.			50	DRAG BUSHING - FRONT	1	452836-1
10	FRONT ANVIL SPACER PLT.			51	DRAG SCREW - FRONT	1	452837-1
11	TOOL SPACER			52	DRAG SPRING - FRONT	1	370572
12	CRIMP SPACER			53			
13	FRONT STRIP GUIDE	1	691311-4	54	FEE MALE BRASS	1	22308-1
14	REAR STRIP GUIDE	1	691311-5	55	ELBOW	1	22317-3
				56	TUBE	1	689446-2
15	RAM	1	471167	57	SCREW, SOC. HD. CAP	1	21001-4
16	TOOL HOLDER	1	689633-2	58			
17	ADJ. CRIMP MOUNT & BLADE MT.	1	465755-2	59	WASHER, LOCK	1	21024-6
18	SCREW SOC. HD. CAP	1	321000-6	60			
19	APPLICATOR MOUNT ASSY.	1	471707-4	61	LUBRICATOR ASSY.	1	465184-2
20	BASE PLATE			62	SYNTHETIC OIL	1	22014-1
21	BASE BLOCK			63	AIR BLAST ASSY.	1	455350-2
22	STRIP GUIDE PLATE			64	MACH. FEED	1	692140-2
23	ANVIL HOLDER			65	TENSION ADJ. PLATE	1	374999
24	AUX. ANVIL HOLDER				MISCELLANEOUS		
25	STRIPPER - GUARD	1	389072-3	66	TOOL SPACER (FOR SET UP ONLY)	1	693619-1
26	STRIPPER MOUNT			67	NOTE: PLACE ITEM 66 BETWEEN CRIMP		
27	RETAINER PLATE			68	HOLDER ITEM 17 & ALIGN.	GA.	
28	STRIPPER MOUNT BRACKET			69			
29	STRIPPER BUSHING			70			
30	STOCK DRAG	1	376666	71			
31	STOCK DRAG HANDLE			72			
32	STOCK DRAG STUD REAR	1	354045-1				
33	STOCK DRAG SPRING REAR	1	123847-1				
34	STOCK DRAG ADJ. SCREW	2	372997				
35	FEED FINGER HOLDER						
36	FEED FINGER	1	452817-1				
37	FEED FINGER TIP						
38	FEED FINGER SPACER						
39	BASE CASTING	1	570238				
40	R GUARD	1	455891-1				
41	F GUARD BOTTOM (RIGHT)	1	810870-1				

REVISION RECORD				DATE	BY	ECN
REV.	LI	ECR-06-002585		2-06	MYE	
F		DELETE 54 CHG 55, 56 PRESS		9-8-75	RL	R 1275
G		13 WAS - 6 14 WAS - 7		11-10-75	RL	R 1382
H		#44 810640-2 WAS - 1		12-10-76	LS/TB	R 1892
J		ECN A-39589Z		9-92	MO/YD	-

CRIMPING DATA				TERMINALS
TO APPLY TERMINAL SPEC 114-2002 FLAT				62001-62201
WIRE SIZE	(2) 17 MAG	CRIMP HEIGHT	.080	
CRIMP WIRE	SIZE .140	TYPE F	FEED	
INSUL. SLEEVED	BLUNT		.315	
INSULATION RANGE	WIRE RANGE CMA 3000-7000			
EXPLODED VIEW	A-6000 6000-5			
REMARKS: SPECIAL 1,800 FORWARD TOP TOOL MOUNTING FROM TOOL HOLDER (16) OUTWARD ITEMS 17, 5 & 1				
■ DENOTES WEARING PARTS RECOMMEND PURCHASE REPLACEMENT				
THIS APPLICATOR IS TO BE USED ON AMP-O-ELECTRIC 1-471273-3				
AMP-O-MATIC MECH. FEED ALIGN. GA. 679597-1				DIST. 4
SERIAL NO.		DATE SHIPPED		DESIGNED BY RUSS PENNETT 10-471
CUSTOMER NAME AND ADDRESS				CHK'D. IKM 11-17-71
				APP'D. 11-22
APPLICATOR NUMBER	REV. LI	566067-1		SHEET 1 OF 1
FOR HARDWARE SEC 7-687500-7				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566067-1](#)