


TERM APPL
SPEC 114-2003

APPLICATOR TO BE USED IN 5-TON BENCHMARKER
P/N 565433-4

-3	2	-1	DWG SIZE	PART NO	DESCRIPTION	ITEM NO
5			← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)			
EQD PER ASSY			PARTS LIST			
IONS IN INCHES. ANCES UNLESS ISE SPECIFIED:			MATERIAL	HEAT TREAT	FINISH	
			11	11	11	
C ±#	DR 12/18/80 APP 5191			AMP AMP Incorporated Harrisburg, Pa.		
C ±#	CHK 1/13/81 REL 6381					
C ±#						
NAME	LENGTHWISE AMPLIVAR SPLICE (PIGTAIL)					ST'D APP'L
TEXTURE: +J						
EX BURRS, BREAK EDGES .01SR MAX	SCALE	DWG NO	SHEET REV			
	1:1	D	566315			
			10/1			



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566315-1](#)