



- ① RECOMMENDED SPARE PARTS.
- ② GREASE LIGHTLY.
- ③ LUBRICATE DAILY USING
NO. 20 MACHINE OIL.
- ④ GUARD MUST BE IN PLACE
WHEN OPERATING APPLICATOR
IN AMP-O-ELECTRIC MACHIN

5. ITEMS WITH QTY OF REF SPECIFIED
(EXCEPT ITEM 79) ARE USED ON
ITEM 46.

66 * Trademark of AMP Incorporated

REF	21045-3	RING,RET "C"(1.187ø)FEED FINGER PIN	124	REF	454220-1	CAP, HOUSING	59	
			123	REF	454485-1	HOUSING	58	
REF	5-21028-1	PIN,SLT SPR(.125øx.50)ADJ ROD	122				57	
1	4-21028-0	PIN,SLT SPR(.093øx.75)ST GUIDE PL	121	1	690542-2	PAWL, FEED	56	
REF	1-21030-1	PIN,DOWEL (.187øx.50)LEVER	120	REF	240624-1	PIN, FEED FINGER	55	
REF	1-21030-6	PIN,DOWEL (.187øx1.25)HOUSING	119	REF	691499-1	SPRING, FEED FINGER	54	
			118	REF	690541-1	FINGER, FEED	53	
2	21024-5	WASHER,LOCK (NO.10)ADJ BLOCK	117	REF	455679-1	LEVER, TERMINAL FEED ARM	52	
REF	21024-5	WASHER,LOCK (NO.10)ADJ PLATE	116	1	811242-2	BUMPER, HOLDDOWN	51	
REF	21024-5	WASHER,LOCK (NO.10)FEED GUIDE ROD	115	1	690753-1	SPACER, TONKER	50	
2	21024-2	WASHER,LOCK (NO.4)FRONT STRIP GUIDE	114	1	7-21002-9	BOLT, CRIMPER (5/16-24x1.00)	49	
			113	1	690602-5	CAM, PRE-FEED 1 1/8 STROKE	48	
			112				47	
4	21024-4	WASHER,LOCK (NO.8)STRIPPER	111	1	459456-1	APPLICATOR, BASIC (SUBASSY)	46	
REF	21899-4	WASHER,FLAT (5/16 DIA)SCREW ADJ	110	1	690191-1	PLUG, NYLON	45	
1	21899-2	WASHER,FLAT (.NO.10)LUB ASSY	109	1	455673-1	RAM	44	
1	21018-5	NUT,HEX (NO.6)HOLDDOWN	108	1	690125-1	WASHER, LAMINATED	43	
REF	21018-5	NUT,HEX (6-32)FEED ADJ	107	1	690124-1	WASHER, RAM	42	
			106				41	
			105	2	23241-6	BALL, STEEL	40	
1	456567-1	SCR,SHLD (.188øx.125)STRIPPER	104	2	690170-1	SPRING, COMPRESSION	39	
1	21009-2	SCR,SKT SET (1/4-20x.25LOC-WEL)RAM	103	1	690142-1	DISC, INSULATION	38	
2	21017-2	SCR,DRIVE (#2x.19)ID PLATE	102	1	4-690141-1	DISC, WIRE	37	
REF	6-23715-5	SCR,PAN HD (6-32x1.50)FEED ADJ	101	1	22480-5	WASHER, SPRING	36	
1	461264-1	PLATE, IDENTIFICATION	100	1	690212-1	POST, RAM	35	
2	2-21002-9	SCR,BHC (10-32x.75)DRAG	99	1	690786-6	SUPPORT, TERMINAL	34	
1	22733-8	SCR,BHC (8-32x.38LOC-WEL)ANVIL	98	REF	455675-1	PLATE, BASE	33	
REF	2-21002-9	SCR,BHC (10-32x.75)CAP	97	1	690432-3	SCREW, ADJUSTMENT	32	
REF	2-22733-8	SCR,BHC (1/4-20x.62)HOUSING	96				31	
REF	2-21002-7	SCR,BHC (10-32x.50)SG ADJ BLOCK	95	REF	455689-1	BLOCK, STRIP GUIDE ADJ	30	
6	2-21002-2	SCR,BHC (8-32x.50)SHEAR	94	1	455671-1	PLATE, STRIP GUIDE	29	
			93	1	1-455888-0	SPACER, FRONT SHEAR DEP	28	
			92	2	1-22284-0	SPRING, DRAG	27	
1	1-21002-7	SCR,BHC (6-32x.38)CAM	91	1	690546-1	LEVER, DRAG RELEASE	26	
			90	1	240792-1	DRAG, STOCK	25	
			89	1	3-690504-5	GUIDE, STRIP (REAR)	24	
			88	1	690438-1	GUIDE, STRIP (FRONT)	23	
			87				22	
1	2-22603-0	SCR,HEX HEAD (8-32x.31)FEED FINGER	86	REF	4-22284-9	SPRING, FEED RETURN	21	
2	1-21000-3	SCR,SKT CAP (4-40x.25)F STRIP GUIDE	85	1	458950-1	ARM, STRIPPER	20	
1	2-21000-7	SCR,SKT CAP (8-32x.50)STRIPPER	84	1	458949-1	STRIPPER	19	
REF	3-21000-7	SCR,SKT CAP (10-32x.75)FEED ROD GD	83				18	
REF	3-21000-6	SCR,SKT CAP (10-32x.62)FEED ADJ BLK	82				17	
2	3-21000-4	SCR,SKT CAP (10-32x.38)SG ADJ BL	81	1	691667-1	GUARD, CHIP (FRONT)	16	
REF	3-21000-4	SCR,SKT CAP (10-32x.38)PIVOT BLOCK	80				15	
REF	455749-1	GUARD, WINDOW	79				14	
1	1-465184-0	LUBRICATOR ASSY	78				13	
REF	852931-2	OIL, LUBRICATING	77	1	5-22280-0	SPRING, SHEAR	12	
1	693183-4	WIRE DEPRESSOR	76	1	690461-1	STOP, SHEAR	11	
1	1-23147-2	SPRING, COMPRESSION	75	1	690459-1	HOLDER, SHEAR (FRONT)	10	
2	690603-1	SPRING, ASSIST	74	1	462006-2	SHEAR, FLOAT (FRONT)	9	
2	23030-1	SCR,SKT CAP (6-32x.25)CP DISC	73	1	1-690514-8	ANVIL	8	
REF	458109-1	WASHER, SPECIAL	72				7	
REF	690517-1	SPACER	71				6	
REF	22594-8	NUT, HEX	70	1	2-455889-0	DEPRESSOR, SHEAR (FRONT)	5	
REF	240628-1	PLATE, ADJUSTMENT	69	1	2-238011-2	SPACER, TUBULAR	4	
REF	240626-1	SHAFT, PIVOT	68	1	5-456135-2	CRIMPER, INSULATION	3	
REF	240633-1	BUSHING	67	1	693184-9	SPACER, CRIMPER	2	
REF	455680-1	LEVER, INTERMEDIATE	66	1	817331-4	CRIMPER, WIRE	1	
REF	240629-1	BLOCK, PIVOT	65	QTY	PART NO	DESCRIPTION	ITEM NO	
REF	240632-2	SCREW, ADJUSTMENT FEED ROD	64	CRIMPING DATA				APPLICATOR WILL APPLY
REF	240659-3	PIN, CAM ROLLER	63	PAD LTR	CRIMP HEIGHT	WIRE SIZE	WIRE STRIP LENGTH	
REF	240658-1	ROLLER, CAM	62	A	.026±.0015	30,28 OR 26	66622-2	
REF	454398-2	ROD, FEED	61	B	NOT	USED		
REF	454178-1	GUIDE, FEED ROD	60	C	NOT	USED		
				D	NOT	USED		
QTY	PART NO	DESCRIPTION	ITEM NO					

REMARKS		NO	REV
		TO APPLY TERMINAL	
APPL USED ON MACHINE PART NO	MACH SERIAL NO	DISTRIBUTION	
CUSTOMER NAME	APPL SERIAL NO	ORIGINAL	
ADDRESS	PURCHASE ORDER	CUSTOMER COPY	
CITY	ENG APP	FIELD ENG COPY	

CRIMP	SIZE	TYPE	FEED	APPL INST		
WIRE	.033	F	.390	AI 8040		
INSUL	.100	0				
WIRE RANGE 30-26	INSULATION RANGE .060-.105		MACHINE NO 565435-5			
REMARKS AMP-0-LECTRIC PRE-FEED OBSOLETE						

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[567304-2](#)