

PRINT

CRIMPING DATA					THIS APPLICATOR WILL APPLY	
PAD LETTER	CRIMP HEIGHT	WIRE SIZE	WIRE STRIP LENGTH	60434		
A	.068	16				
B	.060	18				
C	.056	20				
D	NOT	USED				
CRIMP	SIZE	TYPE	FEED	PRESS REF.		
WIRE	.080	F				
INSULATION	.180	F	1.025	565435-5		
INSULATION RANGE	WIRE RANGE	APPLICATOR	INSTRUCTION	8039	152367	
.090-.130	20-16					
REMARKS						
AMP-O-LECTRIC						
POST FEED						
I.D. PLATE(REF): 461264-1						
SET UP GAGE	LAYOUT NO.	AMP		AMP INCORPORATED		
158638-1				HARRISBURG, PENNA.		
DRAWN	APPROVED	LOC		NO.		
1-31-74	1-31-74	A C		687995-2		
CHECKED	REV.	SCALE		NONE		
1-31-74	1-31-74	NONE		NAME		
MINIATURE QUICK CHANGE APPLICATOR				END-FEED (FAST IN TAB)		

NO. 687995-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[687995-2](#)