


PART NUMBER	FIRST USED	AWG	INS. RANGE		COLOR CODE
			MAX	MIN	
69551	69525-1	28	.045	.026	BLACK
69551-1	69525-1	26	.045	.026	BROWN
69551-2	69525-1	24	.045	.026	RED
69551-4	69525-1	22	.045	.026	ORANGE
69551-5	69525-1	28	.045	.026	BLACK
69551-6	69525-1	26	.045	.026	BROWN
69551-7	69525-1	30	.045	.015	WHITE
69551-8	69525-1	22	.045	.026	ORANGE
69551-9	69525-1	24	.045	.026	RED
1-69551-0	69525-1	30	.045	.015	WHITE
1-69551-1	69525-1	24	.045	.026	RED
1-69551-2	69525-1	24	.045	.026	RED
1-69551-3	69525-1	28	.065	.055	BLACK



DWG. SIZE				NUMBER				NAME				REMARKS				ITEM NO.	
REQUIRED PER ASSEMBLY ©1966 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.														CUSTOMER COPY REFERENCE ONLY			
DR				MATERIAL AND FINISH				CLASS				AMP INCORPORATED HARRISBURG, PENNA.					
CHK				STEEL				ELECTROLESS				NICKEL					
DE				WIRE - RANGE - INSULATION				TYPE				TERMI-POINT					
TOLERANCE EXCEPT				SCALE				LOC				NO					
AS NOTED				1" = 0'				M				B 69551					
NAME				MANDREL				REV				C					

LTR	REVISION RECORD	DR	CHK	DATE
C	REVISED	B.S.		12-27
B	REVISED	F.W.		12-27
A	REVISED	P.L.		12-27

NUMBER	DESCRIPTION
69551	

DIMENSIONS IN INCHES. DO NOT SCALE PRINT

PRINT JUST

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[69551-9](#)