


PART NUMBER	FIRST USED	AWG	INS. RANGE		COLOR CODE
			MAX	MIN	
69551	69525-1	28	.045	.026	BLACK
69551-1	69525-1	26	.045	.026	BROWN
69551-2	69525-1	24	.045	.026	RED
69551-4	69525-1	22	.045	.026	ORANGE
69551-5	69525-1	28	.045	.026	BLACK
69551-6	69525-1	26	.045	.026	BROWN
69551-7	69525-1	30	.045	.015	WHITE
69551-8	69525-1	22	.045	.026	ORANGE
69551-9	69525-1	24	.045	.026	RED
1-69551-0	69525-1	30	.045	.015	WHITE
1-69551-1	69525-1	24	.045	.026	RED
1-69551-2	69525-1	24	.045	.026	RED
1-69551-3	69525-1	28	.065	.055	BLACK



DWG. SIZE		NUMBER	NAME	REMARKS	ITEM NO.
REQUIRED PER ASSEMBLY		©1966 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.		CUSTOMER COPY REFERENCE ONLY	
DR	CHK	DE	MATERIAL AND FINISH STEEL ELECTROLESS NICKEL	AMP INCORPORATED HARRISBURG, PENNA.	
WIRE - RANGE - INSULATION SEE TABLE, SEE TABLE		TYPE		TERMI-POINT	
TOLERANCE EXCEPT AS NOTED ± .015 ± 1° 0'		SCALE	LOC	NO	REV
NAME		MANDREL		C	
REVISION RECORD		DESCRIPTION			
LTR	DR	CHK	DATE		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[69551-6](#)